

RGB/ Mini Coax Compression Connectors

INDUSTRY USE: COMMERCIAL • PROFESSIONAL A/V • SECURITY

- Available in two sizes: RG15 (22-24 AWG), purple and RG1 (25-26 AWG), orange
- F, RCA & BNC connector types
- Multi-piece RGB connectors are for solid center wire or stranded cable
- One-piece RGB connectors are for solid center conductor wire only, allowing installers to save time while retaining quality
- RGB F pin-type connector for RG15 (22-24AWG wire)
- Stringent testing standards demonstrate superior return loss numbers on all our RGB/ mini coax connectors



Nickel Part#	Gold Part#	Connector Description	Tip Req'd	Tool Req'd
FS15		F, 1 Piece Solid Center Cond., RGB 22-24 AWG (Purple)	LMTIP-S	CPLCCT-SLM
FS15BNC	RG15BNC	BNC, 1 Piece Solid Center Cond., RGB 22-24 AWG (Purple)	NONE	CPLCCT-SLM
FS15RCA	RG15RCA	RCA, 1 Piece Solid Center Cond., RGB 22-24 AWG (Purple)	LMTIP-S/G	CPLCCT-SLM
FS1BNC	RG1BNC	BNC, 1 Piece Solid Center Cond., RGB 24-26 AWG (Orange)	NONE	CPLCCT-SLM
FS1RCA	RG1RCA	RCA, 1 Piece Solid Center Cond., RGB 22-24 AWG (Purple)	LMTIP-S/G	CPLCCT-SLM
FSBNC15RGB	RGBNC15RGB	BNC, Multi-Piece, RGB 22-24 AWG (Purple)	NONE	CPLCCT-SLM
FSRCA15RGB	RGRCA15RGB	RCA, Multi-Piece, RGB 22-24 AWG (Purple)	LMTIP-S/G	CPLCCT-SLM
FSBNC1RGB	RGBNC1RGB	BNC, Multi-Piece, RGB 24-26 AWG (Orange)	NONE	CPLCCT-SLM
FSRCA1RGB	RGRCA1RGB	RCA, Multi-Piece, RGB 24-26 AWG (Orange)	LMTIP-S/G	CPLCCT-SLM

NOTE: All cable for ICM compression connectors should be sized using the ICM Cable Sizing Chart located on pg.44 or at www.icmcorp.net/ICM_techinfo.com