



Powering Business Worldwide

pe.eaton.com

Eaton Class I division 2 Assembled control station

10250T706G

UPC:782114504390

Dimensions:

- **Height:** 2.75 IN
- **Length:** 3.5 IN
- **Width:** 2.5 IN

Weight:.4 LB

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Class I Division 2
- **Actuator Color:** Green
- **Actuator Material:** Plastic
- **Bezel:** Chrome
- **Contact Configuration:** 1NO-1NC
- **Illumination:** Non-illuminated
- **Legend:** Blank legend
- **Mounting:** Flush
- **Operating Mode:** Momentary
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D
- **Series:** 10250T

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T706G](#)

Certifications: No Data

Product compliance: No Data

