



Powering Business Worldwide

pe.eaton.com

Limit Switch

10316H1002

UPC:782113230115

Dimensions:

- **Height:** 2.26 IN
- **Length:** 5.21 IN
- **Width:** 2.81 IN

Warranties:

- 1 year

Specifications:

- **Connection:** Screw terminals
- **Contact Rating:** 10A at 240 Vac, 0.1A at 250 Vac
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Die cast aluminum
- **Environmental Rating:** NEMA 7 Division I Class I BCD, NEMA 9 Division I Class II EFG
- **Maximum Ac Current:** 10A continuous
- **Maximum Dc Current:** 0.1A
- **Operating Temperature:** -20° to 200°F (-29° to 93°C)
- **Switch Type:** Standard, 10° pre-travel

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 10316H1002](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data

