



Powering Business Worldwide

pe.eaton.com

E51 Series, Limit Switch Style, Modular Inductive Proximity Sensor

E51PLT56P

UPC:782113335421

Dimensions:

- **Height:** 4.53 IN
- **Length:** 1.54 IN
- **Width:** 1.78 IN

Weight:.9938 LB

Notes:Sensor head features a programmable output selector switch for N.O. or N.C. operation. Sensor body is attached to receptacle with tamper-proof screws.

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 0.3%
- **Connection:** 8 Ft. (2.5m) Cable
- **Contact Rating:** 600 mA
- **Cable Type:** SOOW-A
- **Contact Configuration:** Complementary PNP
Open Collector
- **Cord Length:** 96 FT
- **Enclosure Material:** Receptacle and Housing:
Die Cast Zinc, Head: Plastic
- **Environmental Rating:** NEMA
3,3S,4,4X,6,6P,12,13, IP67
- **Input Voltage:** 10–30 Vdc
- **Led Indicators:** Lights when output is ON. One
LED for each output
- **Operating Mode:** Un-shielded
- **Operating Temperature:** -13° to 158°F (-25° to
70°C)



- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E51PLT56P](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance:

- CE Marked