

# Photoelectric Sensor

13104AS3019



## General Description

Photoelectric Sensor, Back Ground Suppression, Forward Viewing, Background suppression, Output ON, 25 ft cable, 6.6 ft, 100 mA PNP, 250 mA NPN at 10-30 Vdc, PVC, NPN and PNP open collector, 10-30 Vdc

## Warranty

3 Years

## Product Specifications

Package: 5.000 x 0.975 x 6.000 in.

Package Weight: 1.750 lbs.

- 25 ft cable
- NPN and PNP open collector
- Polyurethane Foam (RIM)
- 100 mA PNP, 250 mA NPN
- -40°-158° F
- NEMA 1, 3, 4, 4X, 6, 12, 13, IP69k
- Auto reset S/C
- Auto reset S/C
- Back Ground Suppression
- 6.6 ft
- Background suppression
- 10-30 Vdc
- 100 mA PNP, 250 mA NPN at 10-30 Vdc
- Output ON
- PVC
- Forward Viewing



*Powering Business Worldwide*

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

© 2014 Eaton  
All Rights Reserved  
Printed in USA  
August 2014

Eaton is a registered trademark.

All other trademarks are property of their respective owners.