

What can we help you find?

## HC-4 Product Details

[Share](#)
[Print](#)
[Email](#)



**HC-4**

TE Internal Number: 4-1618274-9

 Active

### High Voltage Relays

Not EU RoHS or ELV Compliant

#### Product Highlights:

- Contact - Arrangement = 1 Form B, SPST-NC, 1 N/C, 1 Form A, SPST-NO, 1 N/O, 1 Form C, SPDT, 1 C/O
- Power Switching = Make Only, Yes, No
- Contact - Rated Current = 0 - 15 A
- Not RF Rated
- Coil - Rated Voltage = 26.5 VDC

[View all Features](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

## Documentation & Additional Information

### Product Drawings:

- None Available

### Catalog Pages/Data Sheets:

- None Available

### Product Specifications:

- None Available

### Application Specifications:

- None Available

### Instruction Sheets:

- None Available

### CAD Files:

- None Available

### Additional Information:

- [Product Line Information](#)

### Related Products:

- [Tooling](#)

## Product Features (Please use the Product Drawing for all design activity)

### Electrical Characteristics:

- [Contact - Rated Current \(A\)](#) = 0 - 15
- [RF Rated](#) = No
- [Coil - Rated Voltage \(VDC\)](#) = 26.5
- [Voltage, Max. \(VDC\)](#) = 0 - 8000

### Termination Features:

- [Termination Style](#) = Turret Terminal
- [High Voltage Connection \(Power\)](#) = Bifurcated Terminals
- [High Voltage Connection \(Coil\)](#) = Turret Terminals

### Body Features:

- [Mount Style](#) = Non-Flanged

### Contact Features:

- [Auxiliary Contacts](#) = Without

### Configuration Features:

- [Contact - Arrangement](#) = 1 Form B, SPST-NC, 1 N/C, 1 Form A, SPST-NO, 1 N/O, 1 Form C, SPDT, 1 C/O
- [Power Switching](#) = Make Only, Yes, No
- [Economizer](#) = Without

### Industry Standards:

- [Government/Industry Qualification](#) = No
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

### Other:

- [Brand](#) = Kilovac