

[My Cart](#) | [My Part Lists](#) | [Sign In/Register](#)[English \(Change\)](#)

What can we help you find?

[Products](#) [Industries](#) [Resources](#) [About TE](#) [My Account](#) [Innovation](#) [Support Center](#)**SP100143WE5 Product Details**[Share](#)[Print](#)[Email](#)**SP100143WE5**

TE Internal Number: E56137-000



Active

Label ID Products

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Labels
- Region = Not Specified
- Printer Type = Thermal Transfer
- Label Height = 36.50 mm
- Label Width = 25.40 mm

[View all Features](#)**Quick Links**

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)**Documentation & Additional Information****Product Drawings:**

- None Available

Catalog Pages/Data Sheets:

- [Wire and Harness ID Products](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)**Product Features (Please use the Product Drawing for all design activity)****Product Type Features:**

- Product Type = Labels
- Self-Laminating = Yes
- UL Listed = No
- Color = Clear (White Printable Area)

Electrical Characteristics:

- [Printer Type](#) = Thermal Transfer
- Web Width (mm [in]) = 87.30 [3.436]

Dimensions:

- Recommended Wire/Cable OD Use Range (mm [in]) = 7.3 [0.287]

Body Features:

- [Material](#) = Polyester
- Horizontal Repeat (mm [in]) = 27.9 [1.1]

Configuration Features:

- [Number of Labels Across](#) = 3

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Printer/Label Features:

- [Label Height](#) (mm [in]) = 36.50 [1.437]
- [Label Width](#) (mm [in]) = 25.40 [1.000]
- [Label Finish](#) = Polyester Overlamine
- Self-Extinguishing = No

Environmental:

- [Operating Temperature](#) (°C [°F]) = -40 - +150 [-40 - +302]

Conditions for Usage:

- Energy Product = No

Packaging Features:

- [Packaging Quantity](#) = 5,000

Product Availability:

- Region = Not Specified

Other:

- Series = SP
- Configurator Part = Yes
- Brand = TE Connectivity

<div>• Tamper Evident = No</div> <div>• Label Type = Die-Cut</div> <div>• Adhesive Type = Permanent Acrylic</div> <div>• Vertical Repeat (mm [in]) = 42.20 [1.661]</div> <div>• Recommended Printer = TE 3000 Series</div> <div>• Printable Height (mm [in]) = 12.70 [0.500]</div> <div>• Recommended Ribbon = 1330-0607-10</div>	
---	--

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

