



SBP100225WE5 Product Details




Label ID Products

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Labels
- Region = Not Specified
- Printer Type = Thermal Transfer
- Label Height = 57.20 mm
- Label Width = 25.40 mm

TE Internal Number: CN9922-000

 Active

SBP100225WE5

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> Std Label (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> None Available <p>CAD Files:</p> <ul style="list-style-type: none"> None Available 	<p>Additional Information:</p> <ul style="list-style-type: none"> Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> Tooling

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> Product Type = Labels Series = SBP Color = Clear (White Printable Area) <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> Printer Type = Thermal Transfer Web Width (mm [in]) = 87.30 [3.436] <p>Body Features:</p> <ul style="list-style-type: none"> Material = Translucent Vinyl Horizontal Repeat (mm [in]) = 27.9 [1.1] Recommended Printer = TE 3000 Series, T200 Recommended Ribbon = TMS-RJS-RIBBON-4RPSCE <p>Configuration Features:</p> <ul style="list-style-type: none"> Number of Labels Across = 3 <p>Industry Standards:</p> <ul style="list-style-type: none"> RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Not reviewed for lead free solder process RoHS/ELV Compliance History = Always was RoHS compliant 	<p>Printer/Label Features:</p> <ul style="list-style-type: none"> Label Height (mm [in]) = 57.20 [2.250] Label Width (mm [in]) = 25.40 [1.000] Label Finish = Gloss/Matte Tamper Evident = No Label Type = Die-Cut Adhesive Type = Permanent Acrylic Vertical Repeat (mm [in]) = 66.70 [2.625] Printable Height (mm [in]) = 19.10 [0.752] <p>Environmental:</p> <ul style="list-style-type: none"> Operating Temperature (°C [°F]) = -51 - +93 [-60 - +200] <p>Conditions for Usage:</p> <ul style="list-style-type: none"> Energy Product = No <p>Packaging Features:</p> <ul style="list-style-type: none"> Packaging Quantity = 5,000 <p>Product Availability:</p> <ul style="list-style-type: none"> Region = Not Specified <p>Other:</p> <ul style="list-style-type: none"> Brand = Raychem