



Main

Device short name	EMA
Provided equipment	Alarm for enable/disable switch
Range of product	SurgeLogic

Complementary

System Voltage	208Y/120 V AC
Device mounting	Flush Surface
Enclosure material	Painted steel
Local signalling	Green normal per phase Red fault per phase
Mounting location	Service entrance
Network number of phases	3 phases
Short-circuit protection	200 kA
Surge current	<= 160 kA per phase
Wiring configuration	3-wire 4-wire

Environment

NEMA degree of protection	NEMA 3R/12
standards	UL 1283 ANSI/IEEE C62.41 ANSI/IEEE C62.45 UL 1449 : ed. 2 UL Category Section 37.3

Offer Sustainability

Not Green Premium product	Not Green Premium product
Will be Compliant on 3Q2014	Will be Compliant on 3Q2014 Will be Compliant on 3Q2014
Reference not containing SVHC above the threshold	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------