



Nothing but **HEAVY DUTY.**

## M18™ Cordless 1/2" Hammer-Drill Driver Kit 2602-22



### The Milwaukee Advantage

The M18™ Cordless 1/2" Hammer Drill Driver not only delivers an industry leading compact and ergonomic design, but is up to 20% faster in concrete than the competition. In addition, the 2602-20 is the only hammer drill/ driver in its class with an all metal gear case, providing maximum durability for heavy duty applications. Built with a Milwaukee® 4-pole motor, the 2602-22 delivers best in class 550 in-lbs of peak torque with the M18™ XC High Capacity LITHIUM-ION Battery, while the 2602-22CT delivers 450 in-lbs of peak torque with the M18™ Compact LITHIUM-ION Battery. A variable speed trigger provides speed control between 0-1,700 RPM (High Speed) & 0-450 RPM (Low Speed).

### Features

Milwaukee® 4-Pole Frameless Motor: Delivers 550 in-lbs of peak torque, 0-450/0-1,700 RPM, & 29,000 BPM.

Compact & Ergonomic Design: 8-1/2" Length

DPM - Digital Power Management: Overload protection prevents damage to the tool and battery in abusive situations

All Metal Gear Case: The only metal gear case in its class

All Metal 1/2" Single Sleeve Ratcheting Chuck: Provides maximum durability and bit retention

### Specifications

Voltage	18V
Torque	550 in-lbs of peak torque
Chuck Type	1/2" Single Sleeve
RPM	0-450/0-1,700
BPM	0-29,000
No of Batteries Included	(2) XC High Capacity LITHIUM-ION Batteries
Battery	LITHIUM-ION
Length	8-1/2"
Tool Weight	4.9 lbs

### Includes

- 2602-22
- (2) XC High Capacity LITHIUM-ION Batteries
- 1-Hour Charger
- Kitbox