



Nothing but **HEAVY DUTY.**

M12™ Cordless No-Hub Driver 2455-22



The Milwaukee Advantage

With specific torque settings for 60 and 80 in/lbs, the M12™ Cordless No-Hub Driver is specifically designed to quickly install no-hub couplings with accuracy and repeatability. The first of its kind in the industry, the 2455-22 can fasten up to 300 clamps on a single charge and is proven to be accurate for up to 25,000 clamps before re-calibration.

Features

Specific Torque Settings for 60 and 80 in-lbs - Fast accurate installation of no-hub couplings

Auto Shut-Off w/ LED Indicator - Alerts users that torque limit has been achieved

LED Calibration Indicator - Alerts user when calibration is needed (25,000 cycles)

0-750 RPM Drill Mode - Increased utility for general drilling and fastening

M12™ LITHIUM-ION Battery Pack - Fastens up to 300 steel clamps on a single charge

Compact/Lightweight Design - Reduces user fatigue at only 2.75 lbs

Specifications

Voltage	12V
No Load Speed	0-250/0-750 RPM
Chuck Type	1/4 Hex
Torque Settings	60 in-lbs and 80 in-lbs
Drill Mode	Yes
On Board Fuel Gauge	Yes
LED Light	Yes
LED Torque Indicator	Yes
LED Calibration Indicator	Yes
Battery	LITHIUM-ION
Charge Time	30 minutes
No of Batteries Included	(2) M12™ LITHIUM-ION Battery Packs
Tool Weight	2.75 lbs
Shipping Weight	7.66 lbs

Includes

- 2455-20 No-Hub Coupling Driver
- (3) Shockwave™ Sockets (1/4", 5/16", 3/8")
- (2) M12™ LITHIUM-ION Battery Packs
- 30-Minute Charger
- Carrying Case