



Nothing but **HEAVY DUTY.**

## M12™ Grease Gun Bare Tool 2446-20



### The Milwaukee Advantage

The M12™ Cordless Grease Gun develops higher pressure, offers greater productivity, and gives the user more versatility on the jobsite than any other cordless grease gun in the market. With up to 25% more pressure and run-time than the competition, the 2446-21XC delivers over 8,000 PSI max operating pressure for heavy duty applications and dispenses up to seven grease cartridges per battery charge. The M12™ Cordless Grease Gun also features a lightweight, ergonomic handle design for greater user comfort during prolonged use and an on board hose storage and shoulder strap loop for added convenience with less mess.

### Features

Powerful 12V Motor: Delivers over 8,000 PSI Max Operating Pressure

Best in Class Run-Time: Dispenses up to 7 cartridges per charge

Superior Handle Balance and Ergonomics: Only 14" long and 7.2 lbs

Integrated Hose Storage and LED Fuel Gauge: Added user convenience and less down time

Air Bleeder Valve: Priming mechanism for quick flow

M12™ Lithium-Ion System: Compatible with over 20 M12™ Lithium-Ion Tools for greater versatility in the workplace

Maximum Durability: Backed by a 5 year warranty

### Specifications

Volts	12V
Output Pressure	Over 8,000 PSI
Run Time	Up to 7 Grease Cartridges per Charge
Grease Capacity	14 oz. Cartridge 16 oz. Bulk
Overload Protection	Yes
Bulk Filler Valve	Yes
Air Bleeder Valve	Yes
Hose Type	36" High Pressure Flex Hose w/ Spring Guard
Three Way Loading	Yes - bulk, cartridge, & suction capable
Coupler Included	Yes
Tool Length	14"
Tool Weight	7.2 lbs
No of Batteries Included	0
Charge Time	30 minutes

### Includes

- 2446-20 Grease Gun
- 36" Flex Hose with Spring Guard, and Grease Couple
- Battery and Charger sold separately