



Nothing but **HEAVY DUTY.**

M12™ Cordless 3/8" Drill Driver 2410-22



The Milwaukee Advantage

The M12™ Cordless 3/8" drill driver delivers 250 in-lbs of torque in a compact light weight design. The only tool in its class with an all metal locking chuck, the 2410-22 drills and fastens up to 35% faster than the competition. The on board fuel gauge displays remaining run-time, while a built in L.E.D. illuminates work surface.

Features

2-Speed (0-1,500/0-400) All Metal Gear Box--Up to 35% faster drilling / fastening and Milwaukee durability

Powerful Motor: Delivers 250 in/lbs of torque-- Up to 25% More Torque

3/8" Single Sleeve ratcheting metal chuck--Increased bit retention and durability

Lightweight and Compact--Tool belt portable at only 2.5lbs and 7-3/8"

Integrated LED and Fuel Gauge-- Increased productivity and decreased frustration.

Specifications

Voltage	12V
Speed	2 Speed
No Load Speed	0-400/0-1,500 RPM
Torque	250 in-lbs
Chuck Type	3/8 in
Single Sleeve	Yes
Metal Sleeve	Yes
Ratcheting Lock	Yes
On Board Fuel Gauge	Yes
LED Light	Yes
Battery	LITHIUM-ION
Length	7-3/8"
On-Board Bit Storage	No
Tool Weight (w/battery)	2.5 lbs
Shipping Weight	7.18 lbs
No of Batteries Included	(2) M12 LITHIUM-ION Batteries
Charge Time	30 minutes

Includes

- 2410 Drill Driver
- (2) M12™ LITHIUM-ION Batteries
- 30 minute charger
- Carrying Case