



What can we help you find?

[Products](#) |
 [Industries](#) |
 [Resources](#) |
 [About TE](#) |
 [My Account](#) |
 [Innovation](#) |
 [Support Center](#)

GTAP-2(B72) Product Details

[Share](#) |
 [Print](#) |
 [Email](#)



GTAP-2(B72)

TE Internal Number: 981609-000

Active

Power Cable Splices, Repair Sleeves and End Seals

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Closure
- GTAP Series
- Closure Type = Hinged
- Connector Included = Yes
- Type of Connector = 4-Port Tap

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • GTAP Gel Tap Slice (PDF, English) <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • GTAP Instructions (PDF, English) <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Closure • Series = GTAP • Closure Type = Hinged • Type of Connector = 4-Port Tap • Cable Type = Polymeric • Retention Type = Snap-lock • Armored Cable = No • Jacketed Cable = With • Package = 72 kits/box <p>Mechanical Attachment:</p> <ul style="list-style-type: none"> • Installation Type = Cold Applied <p>Dimensions:</p> <ul style="list-style-type: none"> • Installed Length (mm [in]) = 108 [4.25] <p>Configuration Features:</p> <ul style="list-style-type: none"> • Connector Included = Yes • Number of Conductors = 1 • Number of Ports = 4 • Conductor (Wire) Size = #14 - 2/0 • Cable Shielding = Without 	<p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant <p>Printer/Label Features:</p> <ul style="list-style-type: none"> • Voltage Rating (kV) = 1 <p>Operation/Application:</p> <ul style="list-style-type: none"> • Application = Above Ground, Direct Burial, Street Lights, Submersible <p>Other:</p> <ul style="list-style-type: none"> • Brand = Raychem • Comment = Kits include connectors