

WIREGRIP CONNECTORS



- Color-coded to industry standards for size selection from 22 - 10 AWG
- Square-wire spring threads provide a positive “Grip” to ensure quick and tight secure connections
- Rated at 600 volt max. for building wiring and 1000 volt max. in lighting fixtures/luminaries and signs (blue and gray WireGrips rated to 300 volt)
- Tough thermoplastic, UL 94V-2 flame-retardant shell at 105°C (221°F)
- UL 486C Listed and CSA 22.2 NO. 188 Certified
- Copper to Copper connections only
- Operating temperature - 105°C (221°F)

Color	Voltage	General Wire Combination Range	Min	Max	Part Number	Quantity
Gray	300V	22 - 14 AWG	2 #22	1 #16 w/1 #18 w/1 #20	CPGI-WC-WG-GR-CL-25	25/Clam
Gray	300V	22 - 14 AWG	2 #22	1 #16 w/1 #18 w/1 #20	CPGI-WC-WG-GR-BG-250	250/BAG
Gray	300V	22 - 14 AWG	2 #22	1 #16 w/1 #18 w/1 #20	CPGI-WC-WG-GR-BG-1000	1000/BAG
Gray	300V	22 - 14 AWG	2 #22	1 #16 w/1 #18 w/1 #20	CPGI-WC-WG-GR-BULK	20,000/Cartron
Blue	300V	22 - 14 AWG	2 #22	3 #16	CPGI-WC-WG-BL-CL-20	20/CLAM
Blue	300V	22 - 14 AWG	2 #22	3 #16	CPGI-WC-WG-BL-BG-150	150/BAG
Blue	300V	22 - 14 AWG	2 #22	3 #16	CPGI-WC-WG-BL-BG-1000	1000/BAG
Blue	300V	22 - 14 AWG	2 #22	3 #16	CPGI-WC-WG-BL-BULK	10,000/Cartron
Orange	600V	22 - 14 AWG	1 #18 w/1 #20	4#16 w/1 #20	CPGI-WC-WG-OR-CL-15	20/CLAM
Orange	600V	22 - 14 AWG	1 #18 w/1 #20	4#16 w/1 #20	CPGI-WC-WG-OR-BG-125	100/BAG
Orange	600V	22 - 14 AWG	1 #18 w/1 #20	4#16 w/1 #20	CPGI-WC-WG-OR-BG-300	300/BAG
Orange	600V	22 - 14 AWG	1 #18 w/1 #20	4#16 w/1 #20	CPGI-WC-WG-OR-BG-500	500/Bag
Orange	600V	22 - 14 AWG	1 #18 w/1 #20	4#16 w/1 #20	CPGI-WC-WG-OR-BULK	5000/Cartron
Yellow	600V	22 - 10 AWG	3 #20 Sol	2 #12 w/2 #14	CPGI-WC-WG-YW-CL-15	15/CLAM
Yellow	600V	22 - 10 AWG	3 #20 Sol	2 #12 w/2 #14	CPGI-WC-WG-YW-BG-100	100/BAG
Yellow	600V	22 - 10 AWG	3 #20 Sol	2 #12 w/2 #14	CPGI-WC-WG-YW-BG-175	175/BAG
Yellow	600V	22 - 10 AWG	3 #20 Sol	2 #12 w/2 #14	CPGI-WC-WG-YW-BG-500	500/Bag
Yellow	600V	22 - 10 AWG	3 #20 Sol	2 #12 w/2 #14	CPGI-WC-WG-YW-BULK	5000/Cartron
Red	600V	22 - 10 AWG	3 #18	2 #10 Sol w/2 #12 Str.	CPGI-WC-WG-RD-CL-12	12/CLAM
Red	600V	22 - 10 AWG	3 #18	2 #10 Sol w/2 #12 Str.	CPGI-WC-WG-RD-BG-100	100/BAG
Red	600V	22 - 10 AWG	3 #18	2 #10 Sol w/2 #12 Str.	CPGI-WC-WG-RD-BG-500	500/Bag
Red	600V	22 - 10 AWG	3 #18	2 #10 Sol w/2 #12 Str.	CPGI-WC-WG-RD-BULK	5000/Cartron
Assort.	Assort.	Assort.	Assort.	Assort.	CPGI-WC-WG-ASRT-CL-20	20/CLAM
Assort.	Assort.	Assort.	Assort.	Assort.	CPGI-WC-WG-ASRT-CL-46	46/CLAM