



What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

GTAP-1(B72) Product Details

- Share
- Print
- Email



GTAP-1(B72)

TE Internal Number: 888615-000

Active

Power Cable Splices, Repair Sleeves and End Seals

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Closure
- GTAP Series
- Closure Type = Hinged
- Connector Included = Yes
- Type of Connector = 4-Port Tap

[View all Features](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

- [Add to My Part List](#)
- [Request Sample](#)
- [Find Similar Products](#)
- [Buy Product](#)

Documentation & Additional Information	
<p><b>Product Drawings:</b></p> <ul style="list-style-type: none"><li>• None Available</li></ul> <p><b>Catalog Pages/Data Sheets:</b></p> <ul style="list-style-type: none"><li>• <a href="#">GTAP Gel Tap Slice</a> (PDF, English)</li></ul> <p><b>Product Specifications:</b></p> <ul style="list-style-type: none"><li>• None Available</li></ul> <p><b>Application Specifications:</b></p> <ul style="list-style-type: none"><li>• None Available</li></ul> <p><b>Instruction Sheets:</b></p> <ul style="list-style-type: none"><li>• <a href="#">GTAP Instructions</a> (PDF, English)</li></ul> <p><b>CAD Files:</b></p> <ul style="list-style-type: none"><li>• None Available</li></ul> <p><a href="#">List all Documents</a></p>	<p><b>Additional Information:</b></p> <ul style="list-style-type: none"><li>• <a href="#">Product Line Information</a></li></ul> <p><b>Related Products:</b></p> <ul style="list-style-type: none"><li>• <a href="#">Tooling</a></li></ul>

Product Features (Please use the Product Drawing for all design activity)	
<p><b>Product Type Features:</b></p> <ul style="list-style-type: none"><li>• Product Type = Closure</li><li>• Series = GTAP</li><li>• Closure Type = Hinged</li><li>• Type of Connector = 4-Port Tap</li><li>• Cable Type = Polymeric</li><li>• Retention Type = Snap-lock</li><li>• Armored Cable = No</li><li>• Jacketed Cable = With</li><li>• Package = 72 kits/box</li></ul> <p><b>Mechanical Attachment:</b></p> <ul style="list-style-type: none"><li>• Installation Type = Cold Applied</li></ul> <p><b>Dimensions:</b></p> <ul style="list-style-type: none"><li>• Installed Length (mm [in]) = 70 [2.75]</li></ul> <p><b>Configuration Features:</b></p> <ul style="list-style-type: none"><li>• Connector Included = Yes</li><li>• Number of Conductors = 1</li><li>• Number of Ports = 4</li><li>• Conductor (Wire) Size = #14 - #2</li><li>• Cable Shielding = Without</li></ul>	<p><b>Industry Standards:</b></p> <ul style="list-style-type: none"><li>• <a href="#">RoHS/ELV Compliance</a> = RoHS compliant, ELV compliant</li><li>• <a href="#">Lead Free Solder Processes</a> = Not relevant for lead free process</li><li>• RoHS/ELV Compliance History = Always was RoHS compliant</li></ul> <p><b>Printer/Label Features:</b></p> <ul style="list-style-type: none"><li>• Voltage Rating (kV) = 1</li></ul> <p><b>Operation/Application:</b></p> <ul style="list-style-type: none"><li>• Application = Above Ground, Direct Burial, Street Lights, Submersible</li></ul> <p><b>Other:</b></p> <ul style="list-style-type: none"><li>• Brand = Raychem</li><li>• Comment = Kits include connectors</li></ul>