

UG1410A



- Resistant to frost, sand and hydrocarbons
- Tactile feedback
- Front panel sealed to IP65 and IP67

### ENVIRONMENTAL SPECIFICATIONS

- Front panel sealing (see drawing opposite) : IP65 and IP67 acc. to IEC 60529
- Salt spray : IEC 512-6, test 11f
- Operating temperature : -20°C to +65°C

### ELECTRICAL AND GENERAL SPECIFICATIONS


- Max. current/voltage rating with resistive load : 2A 24VDC
- Initial contact resistance : 100mΩ max.
- Insulation resistance : 100 MΩ min. at 500VDC
- Dielectric strength : 500 Vrms
- Electrical life at full load : 1.000.000 cycles
- Panel thickness : 7 mm (.276) max.
- Total travel : 1,5 mm (.059) +/- 0,3 mm
- Typical operating force : 7N +/- 2N
- Low level or mechanical life : 1.000.000 cycles
- **Torque : 0,5 to 1Nm max. applied to nut**

### MATERIALS

- Case/bushing : thermoplastic
- Actuator : polyurethane
- Contacts : silver, gold plated
- Multi-wire lead AWG20, section 0,6 mm<sup>2</sup>.
- Terminal seal : epoxy

### PANEL MOUNTING

① Flat seal



IA						
<b>SERIES</b>	<b>Actuator shape</b>	<b>Electrical functions</b>	<b>Terminals</b>	<b>Contacts</b>	<b>Actuator colours</b>	<b>Case colour</b>
	R round	3 Normally open (NO) 5 NC/NO combined	F Flying leads	1 Silver, gold plated	1 Blue 2 Black 3 Green 4 Grey 5 Yellow 6 Red 7/1 White 9 Orange	00 Black

**Dimensions** : First dimensions are in mm while inches are shown as bracketed numbers.



**A sealing boot** is available to protect the switches against frost and sand. See end of this catalogue.



**Mounting accessories** : Standard hardware supplied : 1 hex nut 19 mm (.748) across flats and 1 flat seal. Knurled nut U3327 available on request.




**Packaging unit** : 25 pieces

The company reserves the right to change specifications without notice.


# IA series

Low profile pushbutton switches for harsh environments - bushing Ø 16 mm - momentary



- Panel cut-out Ø 16,2 mm (.657)
- Min. pitch for matrix mounting :
  - with standard hex nut : 27 x 27 mm (1.062 x 1.062)
  - with knurled nut U3327: 20 x 20 mm (.787x.787)

## MODEL STRUCTURE



NO model has 2 terminals only.


## Models



Normally open (NO)  
**IAR3F**



NC/NO combined  
**IAR5F**




Wire colours (NC/NO) : black = common, brown = NC, blue = NO

## CONTACT MATERIAL




1 Silver, gold plated

## ACTUATOR COLOURS



1 : blue - 2 : black - 3 : green - 4 : grey - 5 : yellow - 6 : red - 7/1 : white - 9 : orange

## CASE COLOUR



00 : black