

### **MOUNTING FOOT KITS**



Available in stainless steel or composite material. Kit includes four feet and mounting hardware for all ACCESSPLUS<sup>TM</sup>, D-BOX<sup>TM</sup>, L-BOX<sup>TM</sup> and COMLINE<sup>TM</sup> cabinets.

BULLETIN: A80

Catalog Number	Material
CMFK	Steel
CMFKSS	Stainless Steel
CMTGFT	Composite

## **SCREW PACKAGES**



Screw Packages are for mounting rack panels and equipment to rack angles.

BULLETIN: A80, DACCY, X20

Catalog Number	Color	Description	Pkg. Qty.
ES1224	Silver	12-24 x 5/8 in. combo head	20
ES1224250	Silver	12-24 x 5/8 in. combo head	250
ES1224B	Black	12-24 x 5/8in. combo head	20
ES1224B250	Black	12-24 x 5/8 in. combo head	250
ASM5	Silver	M5 x 20 mm Combo Head	20
ASM6	Silver	M6 x 16 mm combo head	20
ASM5T	Silver	M5 x 12 mm thread-forming Phillips hex head screws	20
ASM6250	Silver	M6 x 16 mm combo head	250
AS1032	Silver	10-32 x 5/8 in. combo head	20
AS1032250	Silver	10-32 x 5/8 in. combo head	250
AS1032B	Black	10-32 x 5/8 in. combo head	20

Use ASM5T on PROLINE™ frame or Net Series extruded holes.

#### **CAGE NUT PACKAGE**



Cage Nut Packages are for use with square-hole rack angles. Cage nuts are plated steel.

BULLETIN: DACCY, P20

Catalog Number	Color	Description	Pkg. Qty.
PM5CN	Silver	M5 cage nut	20
PM6CN	Silver	M6 cage nut	20
PM6CN250	Silver	M6 cage nut	250
P1032CN	Silver	10-32 cage nut	20
P1032CN250	Silver	10-32 cage nut	250
P1224CN	Silver	12-24 cage nut	20
P1224CN250	Silver	12-24 cage nut	250

### **POLE MOUNTING KITS**





Enable COMLINE<sup>TM</sup>, CONCEPT<sup>TM</sup>, ACCESSPLUS<sup>TM</sup>, D-BOX<sup>TM</sup> and L-BOX<sup>TM</sup> enclosures to be mounted to poles of various sizes and shapes. Simply attach the galvanized steel channel bar to the mounting holes at the back of the enclosure, then wrap the stainless steel strap around the pole and through the bar. Kit includes two mounting channels, two straps suitable for up to 12-in. diameter pole, and mounting hardware.

# BULLETIN: CWY

Catalog Number	Fits Enclosure	
CPMK12	when B = 12.00 (305)	
CPMK16	when B = 16.00 (406)	
CPMK20	when B = 20.00 (508)	
CPMK24	when B = 24.00 (610)	
CPMK30	when B = 30.00 (762)	