

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200860102](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Nano-Change (M8) Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 24 AWG, PVC Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E152210

General

Product Family Industrial Cordsets
 Series [120086](#)
 Connector End A Nano-Change (M8)
 Connector End B Pigtail
 IP Rating IP68
 Material - Contact Copper Alloy
 Overview [Brad Nano-Change \(M8\) Products](#)
 Product Name Nano-Change (M8)
 Region America
 Type Single Ended
 UPC 78172553222

Physical

Cable Diameter 4.32mm (.170")
 Cable Length 2.0m (6.56')
 Color - Cable Jacket Yellow
 Coupling Style Threaded
 Gender Female-Pigtail
 Keyway A-coded
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body TPE
 Material - Coupling Nut Nickel-plated Brass
 Material - O-Ring Fluoro-elastomer
 Material - Plating Mating Gold
 Orientation Straight to Pigtail
 Poles 3
 Temperature Range - Operating -20°C to +105°C
 Wire Size AWG 24
 Wire/Cable Type UL 2661

Electrical


Current - Maximum per Contact 4.0A
 Voltage - Maximum 60V AC / 75V DC

Material Info

Engineering Number 403000A10M020

Reference - Drawing Numbers

Sales Drawing 1200860594-000, SD-120086-102



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per -ED/01/2018 (15 January 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120086](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION