



EZ-RJ45® CAT6 Connectors

100010

Product Overview

Product Number: 100010

The new patented EZ-RJ45 CAT6 Connector simplifies twisted pair terminations by allowing the wires to be inserted through the connector and out the front. This allows the technician to easily verify the proper wiring order. Electrical performance of the termination is optimized by pulling the connector down over the cable jacket and seating it tightly in the rear of the connector. By reducing the distance between the wire twists and contacts, performance is optimized! Crimp with the patented EZ-RJ45 Crimp Tool... crimps and trims in one cycle. (See Part Number 100 004 or 100 054 EZ-RJPRO HD). Manufactured in the USA. Patented.

- For use in CAT6 compliant data networks.
- Category 6 performance per EIA/TIA B.2. FCC compliant, UL rated. RoHS compliant
- EZ to verify wire sequence. Simple one piece design...no bars or liners.
- Works with solid or stranded wire.
- Faster terminations with reduced scrap.
- Max Cable OD: 6.60mm (0.260"), Max Insulated wire OD: 1.041mm (0.041")



Part Numbers

Part #	UPC	Description
100010C		EZ-RJ45® CAT6 Connectors, 50 Pc. Clamshell.
100009		EZ-RJ45 CAT6 Connector. 10/Clamshell
100010B		EZ-RJ45® CAT6 Conn., 100 Pc. Box.
100011C		EZ-RJ45® CAT6 Combo. Includes 30 Conn. & 30 Strain Reliefs
105004		EZ-RJ45® CAT6 Connectors, Bulk. Min. 500 Pcs.
202010J		EZ-RJ45® CAT6 Connectors, Jar of 100.