

## ProStrip Wire Strippers

Strip solid  
and stranded,  
Comfort grip,  
feel the  
difference  
Use left or  
right handed



## ProStrip 10/20 & 16/30 Wire Strippers

Designed to meet the demanding expectations of professionals, the new ProStrip wire strippers deliver top performance, total comfort and consistent, reliable results.

- Precision-ground strip nest for clean strips on solid or stranded CU/AL wire
- Durable ergonomic grips reduce hand and wrist fatigue
- Requires less hand force to cut due to geometrically designed handles
- Use left or right handed – wire size marked on both sides of tool
- Non-slip, color-coded handles to quickly distinguish tools
- Lock device protects cutting & stripping edges when stored
- Opening stop prevents spring from coming off and becoming disengaged
- Curved blades for easier cleaner cuts

### Application

- ProStrip 10/20: Cut & strip 10-20 AWG solid and 12-22 AWG stranded
- ProStrip 16/30: Cut & strip 16-30 AWG solid and 18-32 AWG stranded
- Cut and chase threads on 6/32 & 8/32 bolts
- Serrated plier nose for gripping, pulling and twisting
- Holes in jaw for looping wire

### Technical Data

- Body material: S45C
- Steel hardness: HRC 45 +/-2
- Finish: Black Oxide
- Spring material: German SWPA (piano wire)

### Ordering Information

Description	P/N	UPC CODE
ProStrip 10/20	15003C	89974000319
ProStrip 16/30	15005C	89974000320

Phone: 800.749.5783 • 805.532.0145  
Fax: 800.749.5784 • 805.532.0125

668 Flinn Avenue, Unit 21  
Moorpark, CA 93021  
[www.platinumtools.com](http://www.platinumtools.com)

***We Make Connections EZ!***