
# Miniature One-touch Fittings Inch-size One-touch Mini

# Series KJ

Applicable Tubing : ø1/8", ø5/32", ø1/4" Connection Thread : 10-32 UNF, NPT 1/16, NPT 1/8



#### Optimum piping in less space with 20% reduction of the outside

Thread seal is standard.

Copper-free specifications (Electroless nickel plated)

Possible to use from vacuum –100 kPa



#### **Applicable Tubing**

Tubing material	Nylon, Soft nylon, Polyurethane
Tubing O.D.	ø 1/8, ø 5/32, ø 1/4

#### Specifications

Fluid		Air/Water Note)			
Maximum operating p	ressure	1.0 MPa			
Operating vacuum pre	essure	–100 kPa			
Proof pressure		3.0 MPa			
Ambient and fluid tem	perature	-5 to 60°C (Water: 0 to 40°C) (No freezing)			
Thread	Mounting section	ANSI/ASMEB1.20.1-1983 (NTP thread) JIS B 0212 2A, Class 2B (UNF thread)			
	Nut section	JIS B 0212 2A, Class 2B (UNF thread)			
Thread seal (Standard	(k	With thread seal			
Copper-free (Standard	(k	Brass parts are all electroless nickel plated.			
Note) Applicable for	general industrial wate	er. Please consult with SMC if using for other kinds			

of fluid.


Ŋ

Also, the surge pressure must be under the maximum operating pressure.

#### **Principal Parts Material**

Body	Stainless steel 303, C3604BD, PBT
Stud	C3604BD (Thread portion)
Chuck, Guide 2	Stainless steel 304
Release button, Guide 1	POM
Seal, O-ring	NBR
Gasket	Stainless steel 304, NBR

# Series KJ



## A Precautions

Be sure to read before handling. Refer to pages 15-18-3 to 15-18-4 for Safety Instructions and Common Precautions on the products mentioned in this catalog, and refer to pages 15-1-10 to 15-1-11 for Precautions on every series.

#### Interchangeability of Series KJ and KQ

#### A Caution

- 1. Do not use the plug-in KQ Series with the KJ Series, it will not hold.
- 2. For combinations other than the plug-in KQs, they are interchangeable.

## Installation and Removal of One-touch Mini Fittings

#### A Caution Installing of tube

- 1. Cut the tube perpendicularly, using caution not to damage its surface. (Use tube cutter "TK-1", "TK-2" or "TK-3". Do not cut the tube with cutting pliers, nippers, scissors, etc.)
- 2. Grasp the tube, then slowly push it until
- it comes to a stop.
- 3. Then, pull it back gently to make sure that it does not come out.

#### Removing of tube

- (Use one hand for removal.)
- 1. Hold the release button with the thumb and forefinger. L
- 2. Grasp the tube with the remaining three fingers and palm.
- 3. Then, pull out the tube with three fingers and palm while pushing in the release
- button with the thumb and the forefinger.
- 4. To reuse the released tube, cut off the damaged portion of the tube.




### Miniature One-touch Fittings Inch-size One-touch Mini Series KJ

#### Male Connector: KJH

	CEN	
		5
1	Tr	 ī
	Y	F
	÷.	 ł

<10-32 UNF>	Applicable tubing O.D. (inch)	Connection thread (T) UNF NPT	Model	H (Width across flats)	L	A	М	Max. port size	Weight (g)	
		10-32 UNF	KJH01-32	7	16.7	13.6		2.3	2	
	1⁄8	1⁄16	KJH01-33S	9.5	18.8	14.8 *	12.7	2.5	5	
		1⁄8	KJH01-34S	11.11	11.11 13.8 9.8*			2.5	4.7	
		10-32 UNF	KJH03-32	8	17	13.9		2.3	2.4	
	5/ <sub>32</sub>	1⁄16	KJH03-33S	9.5	19.5	15.5 *	-	3	4.7	
		1⁄8	KJH03-34S	11.11	14.8	10.8 *			4.6	
		10-32 UNF	KJH07-32		18.4	15.3		2.3	3.3	
<npt></npt>	1/4	1⁄16	KJH07-33S	11.11	22	18 *	13.6	3.5	6.2	
		1⁄8	KJH07-34S		18.4	14.4 *		4.6	5.2	
		erence dimen	sions after NP	T threa	ad inst	allatio	n.			




#### Hexagon Socket Head Male Connector: KJS

<10-32 UNF>	Applicable tubing O.D. (inch)	Connection thread (T) UNF NPT	Model	H (Width across flats)	Note) ØD	L	A	М	Min. port size	Weight (g)	<10-32 UNF>	<npt></npt>	
	1⁄8	10-32 UNF	KJS01-32	2	7	19.7	16.6	12.7	2	2.8			
		10-32 UNF	KJS03-32	2.5	8	18.7	15.6		2.5	2.7	<del>((</del> ⊕ <b>*</b> ))		
	5/ <sub>32</sub>	1⁄16	KJS03-33S	2.78	-	19.6	15.6 *	12.7	2.8	4			
		1⁄8	KJS03-34S	2.70	10.3	19.0	15.0		2.0	5.4	Applicable tubing	Applicable tubing	
		10-32 UNF	KJS07-32	2.5		19.6	16.5		2.5	3.3	øD/.		
	1/4	1⁄16	KJS07-33S	3.57	10.3	10.3 21.1	21.1	17.1 *	13.6	3.6	5.8		
<npt></npt>		1⁄8	KJS07-34S	4.76		20.1	16.1 *		4.8	5.2			
	/ 11	eference din e) øD: Max.	nensions after diameter	NPT ti	hread	install	ation.						

#### Female Connector: KJF



tubing O.D. (inch)	thread (T) UNF	Model	H (Width across flats)	Note) ØD	L1	L2	м	Min. port size	Weight (g)
1⁄8	10-32 UNF	KJF01-32	7	6.9	18.8	7.9	12.7	2.5	2.8
5/ <sub>32</sub>	10-32 UNF	KJF03-32	8	7.9	18.7	7.8	12.7	3	3.8
1/4	10-32 UNF	KJF07-32	11.11	10.3	18	7.5	13.6	4	5.3
Note	) øD: Max.	diameter							



T (with seal)

#### Straight Union: KJH

- 2000	1		18
	Contraction of the		LB
	1000		P B
	1000		18
			18
			88

Applicable tubing O.D. (inch)	Model	Note) ØD	L	М	Min. port size	Weight (g)			
1⁄8	KJH01-00	8.4	26.3	12.7	2.5	1.4			
5/32	KJH03-00	9.3	26.3	12.7	3	1.7			
1⁄4	KJH07-00	12	28.1	13.6	4.6	2.6			
Note) ØD: Max. diameter									

