
Nylon Tubing

Series T/TIA



For general pneumatic tubing, Nylon tubing Burst Pressure Characteristics Curve and Operating Pressure



A Precautions

Be sure to read before handling.
Refer to pages 15-18-3 to 4 for Safety
Instructions and Common Precautions
on the products mentioned in this
catalog, and refer to pages 15-1-10 to
11 for Precautions on every series.

⚠ Caution

- Applicable for general industrial water. Please consult with SMC if using other kinds of fluid. Surge pressure must be under the max. operating pressure.
 - If the surge pressure exceeds the maximum operating pressure, it will result in damage to fittings and tubes.
- The value of the max. operating pressure is at a temperature of 20°C. Refer to the burst pressure characteristics curve for other temperatures.

Furthermore, abnormal temperature rises caused by adiabatic compression may result in the burst of the tube.

Model/Specifications


 \bullet — 20 m roll \Box — 100 m roll (T1613 is reel.)

	Tubing size														
	Metric size (Series T)								Inch size (Series TIA)						
Model	T0425	T0403	T0604	T0645	T0806	T1075	T1209	T1613	TIA01	TIA05	TIA07	TIA11	TIA13		
Tubing O.D. (mm)	4	4	6	6	8	10	12	16	3.18	4.76	6.35	9.53	12.7		
Tubing I.D. (mm)	2.5	3	4	4.5	6	7.5	9	13	2.18	3.48	4.57	6.99	9.56		
Black (B)		•				_		_	<u> </u>	-	-	-	-		
White (W)		•	_	•	_				-	-	-	-	-		
Red (R)	•		•		•	-	•								
Blue (BU)	•	_	•	_	•	•	•								
Yellow (Y)	•		•		•	•	•								
Green (G)	•		•		•	•	•								
									Nominal size (inch)						
	5/32 "				5/16"				1/8 " 3/16" 1/4 " 3/8 " 1/2 "						
Fluid			·		·		Air/V	Vater	·	·		·			

Fluid	Air/Water Air/Water												
Max. operating pressure (at 20°C)	1.5 MPa												
Burst pressure		Refer to the burst pressure characteristics curve.											
Min. bending radius (mm)	13	25	24	36	48	60	75	100	15	20	30	60	75
Operating temperature	-20 to +60°C (Water: 0 to 40°C) (No freezing)												

How to Order

Nylon 12



Made to Order -

(Please contact SMC for specifications in detail, dimensions, delivery and specifications other than those mentioned above.)

100 m reel Metric size and Inch size except ø16: Suffix "-X3" to the end of part number. Ex.) TS0425R-100-X3

Longer length reel Metric size: Suffix "-X3" to the end of part number. Ex.) TS0425G-500-X3

20 m roll Inch size: Suffix "-X4" to the end of part number. Ex.) TISA01BU-20-X4

Material

Made to Order Availability

Part no.	Length Model	T0425 *	T0604 *	T0806 *	T1075 *	T1209 *	TIA01 *	TIA05 *	TIA07 *	TIA11 *	TIA13 *	Color	
	100 m reel	0	0	0	0	0	0	0	0	0	0	Black, White,	
Х3	150 m reel				0							Red, Blue,	
٨٥	200 m reel			0								Yellow, Green	
	500 m reel	0	0									Tellow, Green	
X4	20 m roll						0	0	0	0	0	Red, Blue, Yellow, Green	