

Stainless Steel 316 One-touch Fittings



Series KQG

Male Connector

India Comission				
Applicable tubing O.D. (mm)	Connection thread	Model		
ø4	M5	KQGH04-M5		
04	R1/8	KQGH04-01S		
	M5	KQGH06-M5		
ø6	R1/8	KQGH06-01S		
	R1/4	KQGH06-02S		
	R1/8	KQGH08-01S		
ø8	R1/4	KQGH08-02S		
	R3/8	KQGH08-03S		
~10	R1/4	KQGH10-02S		
ø10	R3/8	KQGH10-03S		
-10	R3/8	KQGH12-03S		
ø12	R1/2	KQGH12-04S		

Hexagon Socket Head Male Connector

	5	
Applicable tubing O.D. (mm)	Connection thread	Model
~ 4	M5	KQGS04-M5
ø4	R1/8	KQGS04-01S
	M5	KQGS06-M5
ø6	R1/8	KQGS06-01S
	R1/4	KQGS06-02S
	R1/8	KQGS08-01S
ø8	R1/4	KQGS08-02S
	R3/8	KQGS08-03S
ø10	R1/4	KQGS10-02S
010	R3/8	KQGS10-03S
ø12	R3/8	KQGS12-03S
שוע	R1/2	KQGS12-04S

Straight Union

Strangine Strict				
Applicable tubing O.D. (mm)	Model			
ø4	KQGH04-00			
ø6	KQGH06-00			
ø8	KQGH08-00			
ø10	KQGH10-00			
ø12	KQGH12-00			



Male Elbow

- 1110110			
Applicable tubing O.D. (mm)	Connection thread	Model	
ø4	M5	KQGL04-M5	
Ø4	R1/8	KQGL04-01S	
	M5	KQGL06-M5	
ø6	R1/8	KQGL06-01S	
	R1/4	KQGL06-02S	Oh:
	R1/8	KQGL08-01S	
ø8	R1/4	KQGL08-02S	
	R3/8	KQGL08-03S	
~10	R1/4	KQGL10-02S	
ø10	R3/8	KQGL10-03S	
ø12	R3/8	KQGL12-03S	
Ø12	R1/2	KQGL12-04S	

Union Elbow

Applicable tubing O.D. (mm)	Model	
ø4	KQGL04-00	
ø6	KQGL06-00	
ø8	KQGL08-00	
ø10	KQGL10-00	
ø12	KQGL12-00	



Male Branch Tee

Applicable tubing O.D. (mm)	Connection thread	Model	
ø4	M5	KQGT04-M5	
94	R1/8	KQGT04-01S	
	M5	KQGT06-M5	
ø6	R1/8	KQGT06-01S	
	R1/4	KQGT06-02S	W.
	R1/8	KQGT08-01S	0)
ø8	R1/4	KQGT08-02S	
	R3/8	KQGT08-03S	
ø10	R1/4	KQGT10-02S	
010	R3/8	KQGT10-03S	
ø12	R3/8	KQGT12-03S	
کا لا	R1/2	KQGT12-04S	



Union Tee

Applicable tubing O.D. (mm)	Model	
ø4	KQGT04-00	
ø6	KQGT06-00	
ø8	KQGT08-00	
ø10	KQGT10-00	
ø12	KQGT12-00	



Union "Y"

Applicable tubing O.D. (mm)	Model	
ø4	KQGU04-00	
ø6	KQGU06-00	
ø8	KQGU08-00	
ø10	KQGU10-00	
ø12	KQGU12-00	



Bulkhead Union

Applicable tubing O.D. (mm)	Model
ø4	KQGE04-00
ø6	KQGE06-00
ø8	KQGE08-00
ø10	KQGE10-00
ø12	KQGE12-00



Stainless Steel 316 One-touch Fittings Series KQG

Applicable Tubing

Tubing material	FEP, PFA, Nylon, Soft nylon, Polyurethane, Polyolefin Note 3)
Tubing O.D.	ø4, ø6, ø8, ø10, ø12



Specifications

Operating fluid	Air, Water, Steam Note 4)	
Operating pressure range Note 1)	-100 kPa to 1MPa	
Proof pressure	3.0 MPa	
Ambient and Operating fluid temperature Note 2)	-5 to 150°C (No freezing)	
Lubricant	Grease-free specification	
Seal on the threads	With sealant	

Note 1) Please avoid using in a vacuum holding application such as a leak tester, since there is leakage.


Note 2) When using at 120°C or higher, for an extended period of time, we recommend that an inner sleeve be used.

Note 3) In the event of using polyurethane tubing, we recommend the use of an inner sleeve in cases where the tubing is strained.

Note 4) Special FKM that is resistant even when steam is used.

	Tubing model (Material)			Applicable inner sleeve		
Tube size	TU (Polyurethane)	TUS (Soft polyurethane)	TH (FEP)	TL (PFA)	Model	Length
0402	_	_	•	_	TJ-0402	18
0425	•	•	•	_	TJ-0425	18
0403	_	_	-	•	TJ-0403	18
0604	•	•	•	•	TJ-0604	19
0805	•	•	_	_	TJ-0805	20.5
0806	_	_	•	•	TJ-0806	20.5
1065	•	•	-	_	TJ-1065	23
1075	_	_	•	_	TJ-1075	23
1008	_	_	•	•	TJ-1208	0.4
1208	•	•	-	_	10-1200	24
1209	_	_	•	_	TJ-1209	24
1210	_	_	•	•	TJ-1210	24

Construction



No.	Description	Material
1	Release bushing	Stainless steel 316
2	Guide	Stainless steel 316
3	Chuck	Stainless steel 316
4	Seal	Special FKM
5	Male connector body	Stainless steel 316
6	Male elbow body	Stainless steel 316
7	O-ring	Special FKM
8	Stopper ring	Stainless steel 316
9	Stud	Stainless steel 316





Fittings



KQGT BranchTee (Male Branch Tee)



Applicable tube O.D.	Port size	Model	Applicable		Applicable tube O.D.	Port size	Model
inch	NPT	KQGT	mm	R	KQGT		
F/00	10-32UNF	KQGT03-32	4	M5	KQGT04-M5		
5/32	1/8	KQGT03-N01S	4	1/8	KQGT04-01S		
	10-32UNF	KQGT07-32		M5	KQGT06-M5		
1/4	1/8	KQGT07-N01S	6	1/8	KQGT06-01S		
	1/4	KQGT07-N02S		1/4	KQGT06-02S		
	1/8	KQGT09-N01S	8	1/8	KQGT08-01S		
5/16	1/4	KQGT09-N02S		1/4	KQGT08-02S		
	3/8	KQGT09-N03S		3/8	KQGT08-03S		
2/0	1/4	KQGT11-N02S	10	1/4	KQGT10-02S		
3/8	3/8	KQGT11-N03S	10	3/8	KQGT10-03S		
1/2	3/8	KQGT13-N03S	12	3/8	KQGT12-03S		
1/2	1/2	KQGT13-N04S	12	1/2	KQGT12-04S		

KQGH Straight Union



Applicable	Model	Applicable	Model
tube O.D. inch	KQGH	tube O.D. mm	KQGH
5/32	KQGH03-00	4	KQGH04-00
1/4	KQGH07-00	6	KQGH06-00
5/16	KQGH09-00	8	KQGH08-00
3/8	KQGH11-00	10	KQGH10-00
1/2	KQGH13-00	12	KQGH12-00

KQGL **Union Elbow**



Applicable	Model	Applicable	Model
tube O.D. inch		tube O.D. mm	KQGL
5/32	KQGL03-00	4	KQGL04-00
1/4	KQGL07-00	6	KQGL06-00
5/16	KQGL09-00	8	KQGL08-00
3/8	KQGL11-00	10	KQGL10-00
1/2	KQGL13-00	12	KQGL12-00

KQGS Internal **Hexagon Socket**



KQGS09-N02S

KQGS09-N03S

KQGS11-N02S

KQGS11-N03S

KQGS13-N03S

KQGS13-N04S

8

10

12

KQGT **Union Tee**

1/4

3/8

1/4

3/8

3/8

1/2

5/16

3/8

1/2



1/4

3/8

1/4

3/8

3/8

1/2

KQGS08-02S

KQGS08-03S

KQGS10-02S

KQGS10-03S

KQGS12-03S

KQGS12-04S

Ī	Applicable	Model	Applicable tube O.D. mm	Model
	tube O.D. inch	KQGT		KQGT
Ī	5/32	KQGT03-00	4	KQGT04-00
Ī	1/4	KQGT07-00	6	KQGT06-00
	5/16	KQGT09-00	8	KQGT08-00
Ī	3/8	KQGT11-00	10	KQGT10-00
	1/2	KQGT13-00	12	KQGT12-00

KQGU Branch "Y"



Applicable	Model	Applicable tube O.D. mm	Model
tube O.D. inch	KQGU		KQGU
5/32	KQGU03-00	4	KQGU04-00
1/4	KQGU07-00	6	KQGU06-00
5/16	KQGU09-00	8	KQGU08-00
3/8	KQGU11-00	10	KQGU10-00
1/2	KQGU13-00	12	KQGU12-00

KQGH Male Connector



Applicable tube O.D.	tube O.D.		Applicable tube O.D.		Model
inch	NPT	KQGH	mm	R	KQGH
5/32	10-32UNF	KQGH03-32	4	M5	KQGH04-M5
5/32	1/8	KQGH03-N01S	4	1/8	KQGH04-01S
	10-32UNF KQGH07-32	M5	KQGH06-M5		
1/4	1/8	KQGH07-N01S	6	1/8	KQGH06-01S
	1/4	KQGH07-N02S		1/4	KQGH06-02S
	1/8	KQGH09-N01S		1/8	KQGH08-01S
5/16	1/4	KQGH09-N02S	8	1/4	KQGH08-02S
	3/8	KQGH09-N03S		3/8	KQGH08-03S
0/0	1/4	KQGH11-N02S	10	1/4	KQGH10-02S
3/8	3/8	KQGH11-N03S	10	3/8	KQGH10-03S
1/2	3/8	KQGH13-N03S	12	3/8	KQGH12-03S
	1/2	KQGH13-N04S	12	1/2	KQGH12-04S

KQGE Bulkhead Union



Applicable	Model	Applicable	Model
tube O.D. inch	KQGE	tube O.D. mm	KQGE
5/32	KQGE03-00	4	KQGE04-00
1/4	KQGE07-00	6	KQGE06-00
5/16	KQGE09-00	8	KQGE08-00
3/8	KQGE11-00	10	KQGE10-00
1/2	KQGE13-00	12	KQGE12-00

KQGL **Male Elbow**



Applicable tube O.D.	Port size	Model Applicable	Applicable tube O.D.	Port size	Model
ch	NPT	KQGL		R	KQGL
2	10-32UNF	KQGL03-32	4	M5	KQGL04-M5
52	1/8	KQGL03-N01S	4	1/8	KQGL04-01S
	10-32UNF	KQGL07-32		M5	KQGL06-M5
1/4 1/8 KQGL07-N01S 6	1/8	KQGL06-01S			
	1/4	KQGL07-N02S		1/4	KQGL06-02S
	1/8	KQGL09-N01S		1/8	KQGL08-01S
16	1/4	KQGL09-N02S	8	1/4	KQGL08-02S
	3/8	KQGL09-N03S		3/8	KQGL08-03S
0	1/4	KQGL11-N02S	10 12	1/4	KQGL10-02S
3/8	3/8	KQGL11-N03S		3/8	KQGL10-03S
را دا	3/8	KQGL13-N03S		3/8	KQGL12-03S
1/2	1/2	KQGL13-N04S		1/2	KQGL12-04S
	32 /4 16	0.D. NPT 10-32UNF 1/8 10-32UNF 1/8 1/4 1/8 1/4 3/8 1/4 3/8 3/8 3/8	NPT KQGL 10-32UNF KQGL03-32 1/8 KQGL03-N01S 10-32UNF KQGL07-N01S 1/4 KQGL07-N01S 1/4 KQGL07-N02S 1/8 KQGL09-N01S 1/4 KQGL09-N01S 1/4 KQGL09-N03S 1/4 KQGL11-N03S 3/8 KQGL11-N03S 3/8 KQGL13-N03S	NPT KQGL Mmm	NPT KQGL MB NPT KQGL Mm R