DC - 3 WIRE - STANDARD Brass, Nickel Plated (BN), Cylindrical, Threaded, 10-30V DC, 200mA, 1 LED for Output Energized


- Most complete range of Fixed Cable and Quick Disconnect Styles
- Available in normally open (N.O.) and normally closed (N.C.) output configuration
- Industry standard 10-30V DC operating voltage and 200mA output current
- Carries ( € mark


- IEC(529) IP67 (NEMA 1, 3, 4, 6, 12, 13) Protection
- Short Circuit Protection
- Overload Protection
- Reverse Polarity Protection
- Wire Break Resistance
- Temperature Range:
  -25 to 70°C (-13 to 158°F)

	M18 Flush Mount			M18 Non-Flush Mount		
Sensing Distance	5mm (.20 in.)			8mm (.31 in.)		
Cable or Connector Style Cat. No.	Cable	63	65	Cable	63	65
PNP Normally Open	9964-4000	9964-4063	9964-4065	9964-4200	9964-4263	9964-4265
Normally Closed \	9964-4400		9964-4465	9964-4600		9964-4665
NPN Normally Open	9964-4100	9964-4163	9964-4165	9964-4300	9964-4363	9964-4365
Normally Closed 🔭	9964-4500		9964-4565	9964-4700		9964-4765
Ripple Voltage	≤10%	≤10%	≤10%	≤10%	≤10%	≤10%
Voltage Range	10V - 30V	10V - 30V	10V - 30V	10V - 30V	10V - 30V	10V - 30V
Supply Current	≤10 mA	≤10 mA	≤10 mA	≤10 mA	≤10 mA	≤10 mA
Max. Load Current	200 mA	200 mA	200 mA	200 mA	200 mA	200 mA
Voltage Drop Across Sensor	≤2.4V	≤2.4V	≤2.4V	≤2.4V	≤2.4V	≤2.4V
Max. Leakage Currrent	≤10 µA	≤10 µA	≤10 µA	≤10 µA	≤10 µA	≤10 µA
Switching Frequency	1000 Hz	1000 Hz	1000 Hz	500 Hz	500 Hz	500 Hz
Hysterisis	≤15%	≤15%	≤15%	≤15%	≤15%	≤15%
Temperature Drift	≤10%	≤10%	≤10%	≤10%	≤10%	≤10%
Repeatability	.25mm (.01 in.)	.25mm (.01 in.)	.25mm (.01 in.)	.40mm (.016 in.)	.40mm (.016 in.)	.40mm (.016 in.)
Front Cap Material	PBTP	PBTP	PBTP	PBTB	PBTB	PBTB

## **Fixed Cable**

PVC 2m (6ft. 6in.). For 5m (16 ft. 5 in.) cable length, change the last two digits of the part number to 02. For other cable lengths and/or PUR cable, please consult Altech. Supplied with Brass, Nickel Plated (BN) locknuts.





## 63 and 65 Style Connectors

4-pin, Micro style, 12mm (.47 in.) supplied with Brass, Nickel Plated (BN) locknuts. The 63 Connector is clear, offering 360° LED viewing.

