



[Custom
Molded
Rubber](#)



[Custom
Colors!!](#)

[Home](#)

[About PacTec](#)

[Contact Us](#)

Login

[Click Here to Register](#)

Username

Password

[Forget your login info?](#)

[View Cart \(0\)](#)
[Advanced Search](#)
[Connector Search](#)

News

Sign up for our latest news and new product updates!

Email:

LH57-200

External Dimensions: 7.2 x 5.5 x 2.2 in.

PCB Dimensions: 6.7 x 5 x 2.2 in.

Colors: Black
PC Bone

Materials: ABS-94HB
[Material Specs](#)

Components:

- Top and Bottom Covers
- Assembly Screws
- 2 Panels
- 4 Feet



[Custom Colors!!](#)



[Free Samples of
New Products Available!](#)



Copyright 2002-2005 © PacTec Divison of LaFrance Corp. All Rights Reserved.

[Privacy
Policy](#)


| [Shipping
Policies](#)

| [Return
Policies](#)


| [Site
Map](#)




LH57-130





LH57-200





**LH57-130
SECTION B-B**



**LH57-200
SECTION B-B**



**SECTION A-A
LH57-130**



**SECTION A-A
LH57-200**

NOTES:

- PANEL SIZE: (FRONT AND REAR)
- LH57-130 1.307 ± .005 [30.20±0.13] HIGH X 5.170 ± .005 [131.32 + 0.13] WIDE 0.62 ± .005 [1.57 + 0.13] THICK. (IN PANEL GROOVE)
- LH57-200 2.057 ± .005 [52.25±0.13] HIGH X 5.170 ± .005 [131.32+0.13] WIDE 0.62 ± .005 [1.57 + 0.13] THICK. (IN PANEL GROOVE)
- ① EXTERIOR INSERT AREA, FOR IN MOLD MODIFICATION.
 - ② INTERIOR INSERT AREA, FOR IN MOLD MODIFICATION. TYPICAL ON TOP AND BOTTOM COVERS.
 - ③ USABLE PANEL AREA.
 - △4 P.C. CARD .062 [1.57] THICK.
 - △5 P.C. CARD .062 [1.57] THICK.

PACITEC®

LH57-130 & LH57-200
www.pacitecenclosures.com
1-610-361-4231