

High Pass Filters Attenuators

Passives

High Pass Filters

Super suppressing (5-40MHz) high pass filters (54-1000MHz). Available in either in line or ground block style housings.

VSHPF-40



VSHPF-40S



Passband	54-1000MHz
Rejection Band:	5-40MHz
Passband Insertions Loss:	1.0dB Max. @ 54MHz
	0.6dB Max. @ 60-1000MHz
Rejection Band Attenuation:	45dB Min.
Return Loss (In and Out):	16dB Min.
RFI:	130dB

Attenuators

In-line Mini Attenuator Pads are available in 8 values. 'F' male to 'F' female 5-1000MHz performance in a 1.25" body. They are installed with standard 'F' connector tool. (SSTLB)

FLN (*dB)-G



- FLN1G (1dB)
- FLN2G (2dB)
- FLN3G (3dB)
- FLN6G (6dB)
- FLN8G (8dB)
- FLN10G (10dB)
- FLN12G (12dB)
- FLN20G (20dB)