

BNC Connector and Tool

Multi-Ferrule BNC Connector



Why stock two connectors when one can make the connection?

Emerson Network Power has expanded its **AIM-Cambridge** product line to offer several Multi-ferrule Crimp Style 2-Piece BNC connectors.

These commercial grade 2-Piece BNC connectors are designed for use on flexible 50 Ohm coaxial cable and are ideal for use in Test Equipment & Instrumentation, CCTV, PC/LAN. Process Controls applications and more.

They have been designed around MIL-STD-202 with up to a 4GHZ frequency range, and are constructed of quality materials including nickel plated housing, a Delrin dielectric and gold plated brass contacts.

By including multiple ferrules these RoHS compliant connectors are designed to eliminate extra inventory on the shelf, while allowing termination of various cable sizes.

For termination of these connectors, please look at our *Universal Ratchet Crimping Tool* for termination of the below connectors.

AIM-Cambridge Part Number #27-9213 NEW PRODUCT

2-Piece Crimp BNC Plug w/(3) Ferrules for RG-58, RG-59. RG-59 Plenum & RG-6

AIM-Cambridge Part Number #27-9010

2-Piece Crimp BNC Plug w/(2) Ferrules for RG-58, RG-59 & RG-59 Plenum

AIM-Cambridge Part Number #24-9960P

Universal Ratchet Crimping Tool for above connectors

Key Features

- Terminate to wider range of cables

Benefits

- Reduce Inventory
- Superior Performance



#24-9960P