	5	4	3		2		1	
D			Description: Part No: Application: Crimp Tool: Impedance: Frequency Range:	40-9538F Adapter N/A N/A	, DB9F-RJ45, grey	2	DRAWING NO. 40-9538F-CUST REVISIONS 01 OFFICIAL RELEASE 08-10-09 J W T Betty 2009.09.0 08-10-09 J W T 408.00 +08.00	D
С	编号 40.5938F_CIIST 版	LLED DOCUMENT 花本 01 日期 Rel'd Date SEP 14,09	Material: RoHS Compliance	Connector I Jack & Terminal I Screw : Wire L Hood E	DB9 female BP8C modular D-SUB male #4-40 UNC JL1061 26AW G Black plastic			С
В	WITH KEY MAS8 33.4 ±0.2 (1.315 ±.008) 8 0 1 (16 ±0.2 (.630 ±.008)	49.3 ±0.2 1.941 ±.008) •		5-0-9	$\begin{array}{c c} & COLOR CODE \\ & 1 - BLUE \\ 2 - ORANG \\ 35 \pm .004) & 3 - BLACK \\ 4 - RED \\ 5 - GREEN \\ 6 - YELLON \\ 6 \pm 0.1 \\ 6 \pm .004) & 8 - WHITE \end{array}$	GE M N		В
A		37.0 (1.457) 40 (1.575) 5 DIM OUT	TLINE TLINE CTHERW DECIMAL XX XX ANGLES THIS I	SE SPECIFIED JE S mm CHI ± 3 TE ± 0.3 APF ± 0.1 TH ± 0.5° U/M DRAWING WAS PRO	ECKED BY DATE RRY.W 08-10-09 PROVED BY DATE IOMAS 08-10-09	SHEET C	CUSTOMER COPY Connectivity Solutions D ADPTR KIT,DB9F-RJ45,GREY	A
	5	4	3		2		1	J