

◆ Home > 5219831F

Part Number: **5219831F**

### General Description

Series	521
Configuration	3 mm Lens
Description	Discrete LED Lamp
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Single Color
Lens Color	White Diffused

### Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	20mA
Derating	from 50° @ .44mA/°C
Solder Temperature	260° for 5 sec
Operating Temperature	-55 ~ +100
Storage Temperature	-55 ~ +100

### Operating Characteristics

Color	Blue
LED Type	GaN
Luminous Intensity Min	7.1
Luminous Intensity Typical	12.5
Luminous Intensity Max	18
Test Current mA	10mA
Dominant Wavelength Typical	465nm
Power Dissipation Max	90mW



This is a  
RoHS Compliant Product  
To learn more click here