

◆ Home > 5219250F

Part Number: **5219250F**


General Description

Series	521
Configuration	5 mm Lens
Description	Discrete LED Lamp
Package Options	Bulk Packaging
Sizes	5mm
Lamp Type	Single Color
Lens Color	Diffused

Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	25mA
Forward Current Pulsed	90mA
Solder Temperature	260° for 5 sec
Operating Temperature	-20~ +100
Storage Temperature	-55~ +100

Operating Characteristics

Color	 Green
LED Type	Standard Efficiency
Luminous Intensity Min	4.2
Luminous Intensity Typical	12.7
Luminous Intensity Max	21.2
Test Current mA	10mA
Dominant Wavelength Typical	569nm
Power Dissipation Max	135mW



This is a
RoHS Compliant Product
To learn more click here