

Part Number: **5502207F General Description**

Series 550

Configuration 5 mm Lens

Description 5 mm Green Diffused CBI

Package Options Bulk Packaging

Sizes 5mm

Lamp Type Single Color
Viewing Right Angle
Polarity Cathode Right

Lens Style Diffused

LED Centerline 3.00

Absolute Maximum Ratings (Ta = 25°)

Forward Current mA 25mA

Reverse Current 10 @ Vr = 3V

Derating from 40° @ .66 mW/°C

Solder Temperature 260° for 5 sec

Operating Temperature -25 to +85

Storage Temperature -30 to +100

Operating Characteristics

Color Green

LED Type High Efficiency


Luminous Intensity Min 3.6

Luminous Intensity Typical 10

Test Current mA 10mA

Emitted Color Green

Power Dissipation Max 75mW







To learn more click here



550 SERIES 5mm LED CBI® Circuit Board Indicator Sloped Back Housing with Standoffs



Standard Polarity shown in drawing: Cathode right



TOLERANCE NOTE: As noted, otherwise:

- LED Protrusion: <u>+</u>0.41mm [<u>+</u>0.016]
- CBI Housing: +0.20mm [±0.008]

To order any of the 550-xx07 part numbers with Reverse Polarity (Cathode Left), please add -010 to the part numbers shown above.



FEATURES / BENEFITS

- ▲ Multiple CBIs form horizontal LED arrays on 6.35mm (0.250") center-lines.
- ▲ High contrast, UL 94 V-0 rated, black housing
- ▲ Oxygen index: 32%
- ▲ Polymer content: PBT, 0.206 g
- ▲ Housing stand-offs facilitate PCB cleaning
- ▲ Solderability per MIL-STD-202F, method 208F
- ▲ LEDs are safe for direct viewing per IEC 825-1, EN-60825-1
- ▲ Compatible with: 550-xx07 Dual Block and 550-xx07-004 Quad Block

PART NUMBER	COLOR
GENERAL PURPOSE	
550-0207	Green
550-0307	Yellow
550-0407	Red
INTEGRAL RESISTOR	
550-0507	Red, 5V
550-0707	Green, 5V
550-0807	Yellow, 5V
LOW CURRENT	
550-1107	Red
550-1207	Yellow
550-1307	Green
HIGH EFFICIENCY	<u></u>
550-2207	Green
550-2307	Yellow
550-2407	Red
550-2507	Orange
BI-COLOR	
550-3007	Red/Green
550-3107	Yellow/Green
SUPER BRIGHT, DIFFUSED	
550-5107	Red
550-5207	Green
550-5307	Yellow
SUPER BRIGHT, WATER CLEAR (Non-tinted, Non-diffused)	
550-5507	Red
550-5607	Green
550-5707	Yellow



