


### Part Number: 5500707F

### **General Description**

Series	550
Configuration	5 mm Lens
Description	5 mm CBI
Package Options	Bulk Packaging
Sizes	5mm
Lamp Type	Single Color
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Diffused
LED Centerline	3.00

### Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	15mA
Derating	from 50° @ .071V/°C
Solder Temperature	260° for 5 sec
Operating Temperature	-20 to +85
Storage Temperature	-55 to +100






This is a RoHS Compliant Product To learn more click here


### **Operating Characteristics**

Color	Green
LED Type	Integral Resistor
Luminous Intensity Min	2
Luminous Intensity Typical	8
Test Current mA	5V
Emitted Color	Green

# Dialight

# 550 SERIES 5mm LED CBI® Circuit Board Indicator Sloped Back Housing with Standoffs





#### TOLERANCE NOTE: As noted, otherwise:

• LED Protrusion: <u>+</u>0.41mm [<u>+</u>0.016]

• CBI Housing: +0.20mm [+0.008]

To order any of the 550-xx07 part numbers with Reverse Polarity (Cathode Left), please add -010 to the part numbers shown above.



## **FEATURES / BENEFITS**

- Multiple CBIs form horizontal LED arrays on 6.35mm (0.250") center-lines.
- ▲ High contrast, UL 94 V-0 rated, black housing
- ▲ Oxygen index: 32%
- Polymer content: PBT, 0.206 g
- Housing stand-offs facilitate PCB cleaning
- Solderability per MIL-STD-202F, method 208F
- ▲ LEDs are safe for direct viewing per IEC 825-1, EN-60825-1
- ▲ Compatible with: 550-xx07 Dual Block and 550-xx07-004 Quad Block

PART NUMBER	COLOR	
GENERAL PURPOSE		
550-0207	Green	
550-0307	Yellow	
550-0407	Red	
INTEGRAL RESISTOR		
550-0507	Red, 5V	
550-0707	Green, 5V	
550-0807	Yellow, 5V	
LOW CURRENT		
550-1107	Red	
550-1207	Yellow	
550-1307	Green	
HIGH EFFICIENCY		
550-2207	Green	
550-2307	Yellow	
550-2407	Red	
550-2507	Orange	
BI-COLOR		
550-3007	Red/Green	
550-3107	Yellow/Green	
SUPER BRIGHT, DIFFUSED		
550-5107	Red	
550-5207	Green	
550-5307	Yellow	
SUPER BRIGHT, WATER CLEAR (Non-tinted, Non-diffused)		
550-5507	Red	
550-5607	Green	
550-5707	Yellow	