

#### • Home> 5593501007F

Part Number: **5593501007F** 

**General Description** 

Color Bi-Color (Red and Green)

Series 559

Configuration Snap-In Bi-Color PMI

Description Red/Grn. Snap-In LED, .250" Mounting Hole Indicator

Housing Black PBT, UL94V-0

Lamp Type Bi-Color

LED Type 3 Leaded Bi-color Snap-In LED

Mounting Method Snap In

Compliancy Front of Panel, UL94V-0

Termination 24 AWG, 14" Wire Lead

Mounting Hole Size .250"

Panel Thickness 0.031" - 0.062"

Diffused Non-Diffused

Forward Current mA 30 mA

Voltage 1.9/2.2 VDC

Operating Temperature -20 +85

Storage Temperature -55 +100



# 559 Series 2 & 3 Leaded Bicolor Snap-in LED - .250" Mounting Hole **Panel Mount Indicators**



# **FEATURES / BENEFITS**

- RoHS compliant
- Long life typically 100K hours
- Low power consumption uses up to 90% less energy than an incandescent indicator
- Front panel snap-in mounting requires no additional hardware
- No heat generated
- Resistant to shock and vibration
- Available in both 2 or 3 leaded versions
- Termination straight terminals for wire wrapping or lead wire for soldering or optional terminals
- Colors include red/green and yellow /green
- Three leaded version allows for additional color variations

# **APPLICATIONS**

Dialight's 559 series LED panel mount indicator is available with a variety of LEDs including AllnGaP and InGaN technology for high brightness applications, bicolor and integral resistors. These indicators are designed for a variety of applications such as:

- Main and remote power indication
- · Maintenance and warning indication
- Status indication Instrumentation .....and many more!

# **SPECIFICATIONS**


- Voltage requirements:
  - 1.6 2.3 VDC typical (current limiting resistor required)
- Mounting hole size: 0.249 0.252" (6.32 6.40 mm)
- Panel thickness: 0.031 0.062" (.787 1.57 mm)
- Housing: Black housing material meets UL94V-0 and enhances LED contrast

- \*Operating temperature: -20°C to +85°C
- \*Storage temperature: -55°C to +100°C
- Electrical connection
  - Straight terminals for wire wrapping or either 6 or 14 inch 24 AWG lead wire

\*\*24 AWG 6" WIRE LEADS - TERMINATION OPTION 003


3 leads - common cathode

#### STRAIGHT TERMINALS - TERMINATION OPTION 001



\*\*24 AWG 14" WIRE LEADS - TERMINATION OPTION 007 RED WIRE BLACK WIRE 3001 R/G Red Cathode 3001 R/G Red Anode 3201 Y/G Yellow Cathode 3201 Y/G Yellow Anode 500 .281 [7.41] [3.18]

BICOLOR: 559-3501-00X and 559-3601-00X ONLY 3 LEADED 6" WIRE LEADS - TERMINATION OPTION 003 3 LEADED 14" WIRE LEADS - TERMINATION OPTION 007



Dimensions in inches [mm]

Please see back of page for part numbers and additional specifications

\* Based on LED color -Contact factory for details **Dialight Corporation** 

1501 Route 34 South • Farmingdale, NJ 07727 USA

Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com







# 559 Series2 & 3 Leaded Bicolor

**Snap-in LED** - .250" Mounting Hole Panel Mount Indicators

Part Number	Color	Peak Wavelength (nm)	Intensity typ. (mcd)	If typ. (mA)	Vf typ. (V)	Viewing Angle 2Ø 1/2	Maximum DC forward Voltage	Termination	RoHS Compliant
559-3001-001F	Red/ Green	660/565	90/40	20	1.8/2.1	60	40/30	Straight terminals	<b>&gt;</b>
559-3101-001F	Red/ Green	660/565	90/40	20	1.8/2.1	60	40/30	Straight terminals	•
559-3201-001F	Yellow/ Green	585/565	12.6/19	20	2.1/2.1	50	30/20	Straight terminals	<b>&gt;</b>
559-3001-003F	Red/ Green	660/565	90/40	20	1.8/2.1	60	40/30	6 inch wire leads	~
559-3201-003F	Yellow/ Green	585/565	12.6/19	20	2.1/2.1	50	30/20	6 inch wire leads	~
559-3501-003F*	Red/ Green	635/568	5/8	10	1.9/2.2	65	30	6 inch wire leads	~
559-3601-003F*	Yellow/ Green	583/568	20/20	10	2.6/2.2	65	20	6 inch wire leads	~
559-3001-007F	Red/ Green	660/565	90/40	20	1.8/2.1	60	40/30	14 inch wire leads	~
559-3201-007F	Yellow/ Green	585/565	12.6/19	20	2.1/2.1	50	30/20	14 inch wire leads	~
559-3501-007F*	Red/ Green	635/568	5/8	10	1.9/2.2	65	30	14 inch wire leads	~
559-3601-007F*	Yellow/ Green	583/568	20/20	10	2.6/2.2	65	20	14 inch wire leads	~

Typical Operating Characteristics (Ta=25°C)

# **LED Panel Mount Indicator Selection**

Dialight's line of LED Panel Mount Indicators are available in a variety of sizes and options. Please visit our website for more information.

# www.dialight.com

- ▶ .156" (3.96mm) *558 Series*
- .250" (6.35mm) *559 Series*
- 5mm *605 Series*
- 6mm 606 Series
- 7mm 607 Series

- 8mm *608 Series*
- 9mm **609 Series**
- ▶ 10mm *610 Series*
- ▶ 11/16" Watertight *557 Series*
- 1" Watertight 556 Series





# **Dialight Corporation**

1501 Route 34 South • Farmingdale, NJ 07727 USA Tel: (1) 732-919-3119 • Fax: (1) 732-751-5778 • www.dialight.com



<sup>\* 3</sup> Leaded Bicolor - only available with wire leads