

#### • Home> 5596101007F

Part Number: **5596101007F** 

**General Description** 

Color Red Series 559

Configuration Daylight Viewable Snap-In PMI

Description Red Snap-In LED, .250" Mounting Hole Indicator

Housing Black PBT, UL94V-0

Keywords Daylight

LED Type Ultra Bright Snap-In LED

Mounting Method Snap In

Compliancy Daylight-Front of Panel, UL94V-0

Termination 24 AWG, 14" Wire Lead

Mounting Hole Size .250"

Panel Thickness 0.031" - 0.062"

Lens Material Non-Tinted

Diffused Non-Diffused

Luminous Intensity Typical 2100

Forward Current mA 50 mA

Voltage 1.9 VDC

Operating Temperature -30 +85

Storage Temperature -40 +100



# **559 Series** - Daylight Viewable Snap-in LED - .250" Mounting Hole Panel Mount Indicators



#### **FEATURES / BENEFITS**

- RoHS compliant
- ▲ Long life typically 100K hours
- ▲ High Brightness for daylight viewing
- ▲ Non-tinted/Non-diffused
- ▲ Low power consumption uses up to 90% less energy than an incandescent indicator
- ▲ Front panel snap-in mounting requires no additional hardware
- No heat generated
- Resistant to shock and vibration
- Termination straight terminals for wire wrapping or lead wire for soldering or optional terminals
- ▲ Colors include red, green, yellow. orange and blue

#### **APPLICATIONS**

Dialight's 559 series LED panel mount indicator is available with a variety of LEDs including AllnGaP and InGaN technology for high brightness applications, bicolor and integral resistors. These indicators are designed for a variety of applications such as:

- · Main and remote power indication
- Maintenance and warning indication
- Status indication Instrumentation ......and many more!

#### **SPECIFICATIONS**

▲ Voltage requirements:

2.1 - 3.5 VDC typical (current limiting resistor required)

▲ Mounting hole size: 0.249 - 0.252" (6.32 - 6.40 mm)


▲ Panel thickness: 0.031 - 0.062" (.787 - 1.57 mm)

▲ Housing: Black housing material meets UL94V-0 and enhances LED contrast

- ▲ \*Operating temperature: -30°C to +85°C
- ▲ \*Storage temperature: -40°C to +100°C
- ▲ Electrical connection

Straight terminals for wire wrapping or either

6 or 14 inch 24 AWG lead wire



Dialight reserves the right to make changes at any time in order to supply the best product possible.

\* Based on LED color -Contact factory for details

Please see back of page for part numbers and additional specifications.





**Dialight Corporation** 



# 559 Series - Daylight Viewable Snap-in - .250" Mounting Hole LED Panel Mount Indicators

### **NON-TINTED/NON-DIFFUSED**

Part Number	Color	Peak Wavelength (nm)	Intensity typ. (mcd)	If typ. (mA)	Vf typ. (V)	Viewing Angle 2Ø 1/2	Max. forward current (mA)	Termination	RoHS Compliant
559-5901-001F	Amber	592	3100	20	2.0	15	50	Straight terminals	<b>~</b>
559-6001-001F	Blue	470	1500	20	3.6	30	30	Straight terminals	<b>~</b>
559-6101-001F	Red	635	2100	20	1.9	15	50	Straight terminals	<b>~</b>
559-6201-001F	Green	525	2200	20	3.5	30	30	Straight terminals	<b>*</b>
559-6301-001F	Orange	605	1300	20	1.9	15	45	Straight terminals	<b>*</b>
559-6401-001F	White	*	600	20	3.5	45	30	Straight terminals	<b>~</b>
559-5901-003F	Amber	592	3100	20	2.0	15	50	6 inch wire leads	<b>~</b>
559-6001-003F	Blue	470	1500	20	3.6	30	30	6 inch wire leads	<b>*</b>
559-6101-003F	Red	635	2100	20	1.9	15	50	6 inch wire leads	<b>*</b>
559-6201-003F	Green	525	2200	20	3.5	30	30	6 inch wire leads	<b>*</b>
559-6301-003F	Orange	605	1300	20	1.9	15	45	6 inch wire leads	<b>*</b>
559-6401-003F	White	*	600	20	3.5	45	30	6 inch wire leads	<b>*</b>
559-5901-007F	Amber	592	3100	20	2.0	15	50	14 inch wire leads	<b>~</b>
559-6001-007F	Blue	470	1500	20	3.6	30	30	14 inch wire leads	<b>~</b>
559-6101-007F	Red	635	2100	20	1.9	15	50	14 inch wire leads	<b>~</b>
559-6201-007F	Green	525	2200	20	3.5	30	30	14 inch wire leads	<b>~</b>
559-6301-007F	Orange	605	1300	20	1.9	15	45	14 inch wire leads	<b>~</b>
559-6401-007F	White	*	600	20	3.5	45	30	14 inch wire leads	<b>~</b>

Typical Operating Characteristics (Ta=25°C)

\* White Color Coordinates

Min Max
X 0.23 0.39
Y 0.22 0.42

## **LED Panel Mount Indicator Selection**

Dialight's line of LED Panel Mount Indicators are available in a variety of sizes and options.

- ▶ .156" (3.96mm) *558 Series*
- .250" (6.35mm) *559 Series*
- ▶ 5mm *605 Series*
- ▶ 6mm 606 Series
- 7mm *607 Series*

- ▶ 8mm 608 Series
- 9mm *609 Series*
- ▶ 10mm *610 Series*
- ▶ 11/16" Watertight *557 Series*
- 1" Watertight 556 Series

**Dialight Corporation** 



