


Home > 5571503203F

Part Number: **5571503203F**

General Description

Color	 Red
Series	557
Description	Red Watertight LED Indicator, 11/16" Mounting Hole
Housing	White polycarbonate
Keywords	Watertight
LED Type	Super Bright
Mounting Method	Nut and Washer
Compliance	Watertight-Front of Panel, MIL-L-3661B
Termination	24 AWG 6" Wire Lead
Terminal Other	Watertight
Mounting Hole Size	11/16"
Panel Thickness	.156 [3.96]
Bezel Finish	Black Anodize
Lens Style	Flat Lens
Lens Material	polycarbonate
Forward Current mA	20 mA
Voltage	12 VDC
Operating Temperature	-25 +85
Storage Temperature	-30 +100

Dialight

557 Series

High Intensity LED Panel Mount Indicators for $1\frac{1}{16}$ " Mounting Hole Watertight



FEATURES / BENEFITS

- ▲ RoHS compliant
- ▲ Daylight viewability
- ▲ Tamperproof /Designed for high durability
- ▲ Long life, up to 100k hours
- ▲ Uniform illumination
- ▲ Low profile flat lens design


APPLICATIONS

The 557 Series LED Panel Mount Indicators incorporate both InGaN and AlInGaP technologies to offer higher intensities. This is a highly durable package, designed to withstand outdoor applications susceptible to rain, dust, and sunlight.

- Instrument panels
- Safety applications
- Vending, gaming
- Lane control
- Transportation - rail, bus, airline
... and many more!

SPECIFICATIONS

- ▲ Available in red, yellow, green, blue, and white
- ▲ Voltage range of 5, 12, 24 VDC
- ▲ Housing material: White polycarbonate
- ▲ Lens material: Polycarbonate 94 - VO
- ▲ Watertight seal from front of panel meets MIL-L-3661B
Maximum mounting torque - 15 in./lb.
- ▲ Front mounting in $1\frac{1}{16}$ " clearance hole
- ▲ Operating temperature: -25°C to $+85^{\circ}\text{C}$
- ▲ Storage temperature: -30°C to $+100^{\circ}\text{C}$



Dialight reserves the right to make changes at any time in order to supply the best product possible.

Please see back of page for part numbers and additional specifications.



Dialight Corporation



557 Series High Intensity LED Panel Mount Indicators for 1¹/₁₆" Mounting Hole Watertight

PART NUMBER	COLOR	VOLTAGE (VDC)	CURRENT (mA)	TYPICAL INTENSITY (fL)	RoHS COMPLIANT
557-1502-203F	Red	5	80	1000	✓
557-1602-203F	Green	5	16	1000	✓
557-1702-203F	Yellow	5	80	1000	✓
557-1802-203F	Blue	5	16	250	✓
557-1002-203F	White	5	16	700	✓
557-1503-203F	Red	12	20	1000	✓
557-1603-203F	Green	12	16	1000	✓
557-1703-203F	Yellow	12	20	1000	✓
557-1803-203F	Blue	12	16	250	✓
557-1003-203F	White	12	16	700	✓
557-1505-203F	Red	24	20	1000	✓
557-1605-203F	Green	24	16	1000	✓
557-1705-203F	Yellow	24	20	1000	✓
557-1805-203F	Blue	24	16	250	✓
557-1005-203F	White	24	16	700	✓

LED Panel Mount Indicator Selection

Dialight's line of LED Panel Mount Indicators are available in a variety of sizes and options.

- ▶ .156" *558 Series*
- ▶ .250" *559 Series*
- ▶ 5mm *605 Series*
- ▶ 6mm *606 Series*
- ▶ 7mm *607 Series*
- ▶ 8mm *608 Series*
- ▶ 9mm *609 Series*
- ▶ 10mm *610 Series*
- ▶ 11/16" Watertight *557 Series*
- ▶ 1" Watertight *556 Series*

Custom capabilities: Please contact factory regarding customizing these indicators to your specific requirement.

Dialight reserves the right to make changes at any time in order to supply the best product possible.

Dialight Corporation



A4703



ISO 9001

Dialight Corporation

