

Home> 5571603203F

Part Number: **5571603203F** 

**General Description** 

Color Green
Series 557

Description Green Watertight LED Indicator, 11/16" Mounting Hole

Housing White polycarbonate

Keywords Watertight

LED Type Super Bright

Mounting Method Nut and Washer

Compliancy Watertight-Front of Panel, MIL-L-3661B

Termination 24 AWG, 6" Wire Lead

Terminal Other Watertight

Mounting Hole Size 11/16"

Panel Thickness .156 [3.96]

Bezel Finish Black Anodize

Lens Style Flat Lens

Lens Material polycarbonate

Forward Current mA 16 mA

Voltage 12 VDC

Operating Temperature -25 +85

Storage Temperature -30 +100



# 557 Series High Intensity LED Panel Mount Indicators for 11/16" Mounting Hole Watertight



### **FEATURES / BENEFITS**

- ▲ RoHS compliant
- Daylight viewability
- ▲ Tamperproof /Designed for high durability
- ▲ Long life, up to 100k hours
- ▲ Uniform illumination
- ▲ Low profile flat lens design


### **APPLICATIONS**

The 557 Series LED Panel Mount Indicators incorporate both InGaN and AllnGaP technologies to offer higher intensities. This is a highly durable package, designed to withstand outdoor applications susceptible to rain, dust, and sunlight.

- Instrument panels
- Lane control
- Safety applications
- Transportation rail, bus, airline
- Vending, gaming
- ... and many more!

### **SPECIFICATIONS**

- Available in red, yellow, green, blue, and white
- ▲ Voltage range of 5, 12, 24 VDC
- Housing material: White polycarbonate
- ▲ Lens material: Polycarbonate 94 VO
- ▲ Watertight seal from front of panel meets MIL-L-3661B Maximum mounting torque 15 in./lb.
- ▲ Front mounting in ¹¹/₁6" clearance hole
- ▲ Operating temperature: -25°C to +85°C
- ▲ Storage temperature: -30°C to +100°C



Dialight reserves the right to make changes at any time in order to supply the best product possible.

Please see back of page for part numbers and additional specifications.









# 557 Series

# High Intensity LED Panel Mount Indicators for <sup>11</sup>/<sub>16"</sub> Mounting Hole **Watertight**

PART NUMBER	COLOR	VOLTAGE (VDC)	CURRENT (mA)	TYPICAL INTENSITY (fL)	RoHS COMPLIANT
557-1502-203F	Red	5	80	1000	~
557-1602-203F	Green	5	16	1000	~
557-1702-203F	Yellow	5	80	1000	~
557-1802-203F	Blue	5	16	250	~
557-1002-203F	White	5	16	700	~
557-1503-203F	Red	12	20	1000	~
557-1603-203F	Green	12	16	1000	~
557-1703-203F	Yellow	12	20	1000	~
557-1803-203F	Blue	12	16	250	~
557-1003-203F	White	12	16	700	~
557-1505-203F	Red	24	20	1000	~
557-1605-203F	Green	24	16	1000	~
557-1705-203F	Yellow	24	20	1000	~
557-1805-203F	Blue	24	16	250	~
557-1005-203F	White	24	16	700	~

## **LED Panel Mount Indicator Selection**

Dialight's line of LED Panel Mount Indicators are available in a variety of sizes and options.

- ▶ .156" *558 Series*
- ▶ .250" *559 Series*
- ▶ 5mm 605 Series
- ▶ 6mm 606 Series
- ▶ 7mm *607 Series*

- ▶ 8mm 608 Series
- ▶ 9mm 609 Series
- ▶ 10mm 610 Series
- ▶ 11/16" Watertight 557 Series
- ▶ 1" Watertight 556 Series

Custom capabilities: Please contact factory regarding customizing these indicators to your specific requirement.

Dialight reserves the right to make changes at any time in order to supply the best product possible.





