

Home > 5219673F

## Part Number: 5219673F

**General Description** 

Series	521
Configuration	5 mm Lens
Description	LED 5 mm Y-Flangeless
Package Options	Bulk Packaging
Sizes	5mm
Lamp Type	Single Color
Lens Color	Diffused





This is a RoHS Compliant Product To learn more click here

## Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	20mA
Reverse Current	100 @ Vr = 5V
Forward Current Pulsed	80mA
Derating	from 25° @ .25mA/°C
Solder Temperature	260° for 5 sec
Operating Temperature	-55~+100
Storage Temperature	-55~+100

## **Operating Characteristics**

Color	Yellow
LED Type	GaAsP/GaP
Luminous Intensity Min	3.5
Luminous Intensity Typical	12.3
Test Current mA	20mA
Power Dissipation Max	60mW