This browser does not have Java enabled.

Supplier Portal


Privacy Policy

Terms & Conditions

Careers



What can we help you find?



Have a Question? Chat with a Product Information Specialist

Manage Your Account

Product Compliance Support Center

Site Map

Keep Me Informed

	THIS DRAWING IS U	4 Inpublished.	RELEASED FOR PU	BLICATION - ,	3		
С	C COPYRIGHT -	NOTES: 1. ELECTRICAL DATA: 2. ENVIRONMENTAL: 3. PACKAGING: 4. SEAL FOR CABLE C 5. FOR TECHNICAL DAT	CONTACT RESISTANCE: INSULATION RESISTANCE: CURRENT RATING: BREAKDOWN VOLTAGE: OPERATING TEMPERATUR SEALING REQUIREMENTS: 107–3334 DD: Ø4.5mm – Ø6.5mm TA REFER TO YOUR LOCAL	CHTS RESERVED. 10 mOhm MAX 100 MOhm MIN at 500VDC 5 AMPS (FOR 3, 4 AND 5 POSITIC 500 VAC MIN PER MINUTE E: -25°C TO +90°C	NS) AND 2 AMPS (FOF	R 8 POSITION ONLY)	
						5	
	<u>P</u>	<u>1838274–1</u> IN ASSIGNMENTS FRONT VIEW		<u>1838274–2</u> <u>PIN ASSIGNMENTS</u> <u>FRONT VIEW</u>	PIN <u>F</u>	<u>838274–3</u> ASSIGNMENTS RONT_VIEW	<u>1838274–4</u> <u>PIN ASSIGNMEN FRONT VIEW</u>
Ą							

\cap	

LOC		DIST		REVISIONS							
E	E B P LTR		DESCRIPTION			DATE	DWN	APVD			
C1		REVISED PER ECO-11-005150		21	MAR11	RK	HMR				
ITEM	DECO		M DESCRIPTION M		MATERIAL		QUANTITY / ITEM				
IIEM		DESCR	KIP II	UN	MATERIAL	FINISH/COLOUR	- 1	-2		-3	
1	CC	ONNECTO	RΗ	OUSIN	G GF NYLON	BLACK	1	1		1	
2	GA	SKET	TOR BODY		SILICONE	BLACK	1	1		1	
3	CC	ONNECTO			GF NYLON	BLACK	1	1		1	
4	SE	EALING N	G NUT		GF NYLON	BLACK	1	1		1	
5	SE	EAL			EPDM	BLACK	1	1		1	
6	SC	OCKET C	ONTA	ACT	BRASS	0.15µm GOLD OVER NICKEL	3	4		5	
7	SC	CREW NUT			ZINC DIE CAST	2.5µm NICKEL PLATED	1	1		1	
8	'0	'RING			VITON	GREEN	1	1		1	

16


1


С

g 1838274









SEALING COMPOUND

1.

 $\overline{7}$

<u>-4</u> ENTS EW					
		M12 FIELD SERVICEABLE CONNECTOR, FEMALE SOCKET, SOLDER TYPE	8 1838274-4		
\sim		M12 FIELD SERVICEABLE CONNECTOR, FEMALE SOCKET, SOLDER TYPE	5 1838274-3		
\sum		M12 FIELD SERVICEABLE CONNECTOR, FEMALE SOCKET, SOLDER TYPE	4 1838274-2		
		M12 FIELD SERVICEABLE CONNECTOR, FEMALE SOCKET, SOLDER TYPE	3 1838274-1		
		DESCRIPTION	NO. OF POS PART NUMBER		
	THIS DRAWING IS A CONTROLLED DOCUMENT. A.Morey CHK F.Wheeler-Kin		E Connectivity	A	
	DIMENSIONS. mm 0 PLC 1 PLC 2 PLC + - - - - - - - - - - - - -	12APR06 NAME			
	3 PLC ± - APPLICATION SPEC 4 PLC ± - - MATERIAL FINISH WEIGHT _	size cage code drawing no A2 00779 C = 1838274	RESTRICTED TO		
	CUSTOMER DE		SHEET 1 OF 1 REV C 1		