

Have a Question? Chat with a Product Information Specialist

What can we help you find?

Email

**Products Industries** Resources **About TE** My Account **Innovation Support Center** 

# 188834-1 Product Details



#### 188834-1

TE Internal Number: 188834-1 Active



### **2mm Hard Metric PCB Mount Connectors** (Z-PACK 2mm HM)

Not EU RoHS or ELV Compliant (Find RoHS Compliant Alternates)

#### **Product Highlights:**

- Connector
- Connector Assembly
- Connector Style = Plug
- Type = Type A
- Interface Type = 2mm HM

View all Features

#### **Quick Links**

Share

- Pricing & Availability
- Search for Tooling
- ▶ View Mating Products (1)
- Product Feature Selector
- Contact Us About This Product

Print

Add to My Part List

Request Sample Find Similar Products

#### **Buy Product**

#### **Documentation & Additional Information**

#### **Product Drawings:**

MALE ASSEMBLY, Z-PACK 2mm HM, TYPE A (PDF, English)

#### Catalog Pages/Data Sheets:

None Available

## **Product Specifications:**

• Z-Pack 2 mm HM CONNECTORS (PDF, English)

#### **Application Specifications:**

• Z-PACK 2mm HM Interconnection System for Board-to-Bo... (PDF, English)

## **Instruction Sheets:**

None Available

## CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version F)
- 3D Model (IGES, Version F)
- 3D Model (STEP, Version F)

#### **Additional Information:**

Product Line Information

#### **Related Products:**

- Tooling
- Mating Products (1)

List all Documents

## Product Features (Please use the Product Drawing for all design activity)

## **Product Type Features:**

- Product Type = Connector
- Connector Type = Connector Assembly
- PCB Mounting Orientation = Vertical

## **Mechanical Attachment:**

- Board Mount = Fixed Board
- Front Mating Level = Level 1

## **Termination Features:**

- Interface Type = 2mm HM
- Termination End Plating = Tin-Lead over Nickel

## **Dimensions:**

• Module Length (mm [in]) = 50.00 [1.968]

### **Body Features:**

Type = Type A

# **Housing Features:**

- Connector Style = Plug
- Mating Alignment = With
- Mating Alignment Type = Multi-Purpose Center
- Housing Color = Gray
- Housing Material = Polyester GF

## **Configuration Features:**

- Number of Rows = 5+2
- Number of Positions = 154
- Crosstalk Version = Standard
- Shielded = Yes
- Rows Loaded = E, F, Z, D, C, B, A
- Shield Type = Ground Return Shielding

## **Industry Standards:**

• RoHS/ELV Compliance = Not ELV/RoHS compliant

• CompactPCI Designation = P1/P4

## **Contact Features:**

- Contact Configuration = Signal
- Feedthrough Post Length (mm [in]) = 3.70 [0.145]
- CompactPCI = Yes
- Contact Plating, Mating Area, Material = Performance-Based
- Grounding Contact = Without
- Contact Style = Short Tail
- Number of Signal Contacts = 110
- Contact Base Material = Phosphor Bronze

- Lead Free Solder Processes = Not relevant for lead free process
- UL Flammability Rating = UL 94V-0

## Other:

Brand = AMP

**Corporate Information** 

About TE
Investors
News Room
Supplier Portal
Careers

Terms & Conditions Privacy Policy

AODA Accessibility Policy AODA Multi-Year Accessibility Plan **Quick Links** 

Distributor Inventory Product Cross Reference Documents & Drawings

**Product Compliance Support Center** 

Site Map

**Customer Support** 

Email or Chat With Us Find a Phone Number Knowledge Base Manage Your Account

**Keep Me Informed** 



© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved

H Provide Website Feedback



