

Have a Question? Chat with a Product Information Specialist

What can we help you find?

Email

Products Industries Resources About TE My Account Innovation Support Center

5352068-1 Product Details



5352068-1

TE Internal Number: 5352068-1



View 3D PDF

2mm Hard Metric PCB Mount Connectors (Z-PACK 2mm HM)

Always EU RoHS/ELV Compliant

(Statement of Compliance)

- Product Highlights:Connector
- Connector Assembly
- Connector Style = Receptacle
- Type = Type A
- Interface Type = 2mm HM

View all Features

Quick Links

Share

- Pricing & Availability
- Search for Tooling
- ▶ View Mating Products (8)
- Product Feature Selector
- ▶ Contact Us About This Product

Print

Add to My Part List Request Sample Find Similar Products

Buy Product

Documentation & Additional Information

Product Drawings:

 Z-PACK 2mm HM TYPE A - 25 COLUMNS PRE-SHIELDED RECEP... (PDF, English)

Catalog Pages/Data Sheets:

None Available

Product Specifications:

• Z-Pack 2 mm HM CONNECTORS (PDF, English)

Application Specifications:

 Z-PACK 2mm HM Interconnection System for Board-to-Bo... (PDF, English)

Instruction Sheets:

None Available

CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version A)
- 3D Model (IGES, Version A)
- 3D Model (STEP, Version A)

Additional Information:

Product Line Information

Related Products:

- Tooling
- Mating Products (8)

List all Documents

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Connector Type = Connector Assembly
- PCB Mounting Orientation = Right Angle

Mechanical Attachment:

• Board Mount = Free Board

Termination Features:

- Interface Type = 2mm HM
- Termination End Plating = Tin over Nickel

Dimensions:

• Module Length (mm [in]) = 50.00 [1.968]

Body Features:

Housing Features:

- Connector Style = Receptacle
- Mating Alignment = With
- Mating Alignment Type = Multi-Purpose Center
- Housing Color = Gray
- Housing Material = Polyester GF

Configuration Features:

- Number of Rows = 5
- Number of Positions = 110
- Crosstalk Version = Standard
- Shielded = Yes
- Rows Loaded = C, B, A, D, E
- Shield Type = Ground Return Shielding
- Shield Style = Upper

• Type = Type A

• CompactPCI Designation = J1, J4

Contact Features:

• Contact Configuration = ACTION PIN Post, Signal

• Feedthrough Post Length (mm [in]) = 3.70 [0.145]

CompactPCI = Yes

 Contact Plating, Mating Area, Material = Performance-Based

• Grounding Contact = Without

Contact Style = Short Tail

Number of Signal Contacts = 110

• Contact Base Material = Phosphor Bronze

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- UL Flammability Rating = UL 94V-0

Other:

- Brand = AMP
- Comment = Female connector with pre-installed shield.

Corporate Information

About TE Investors News Room Supplier Portal Careers

Careers
Terms & Conditions
Privacy Policy
AODA Accessibility Policy
AODA Multi-Year Accessibility
Plan

Quick Links

Distributor Inventory
Product Cross Reference
Documents & Drawings

Product Compliance Support Center

Site Map

Customer Support

Email or Chat With Us Find a Phone Number Knowledge Base Manage Your Account

Keep Me Informed



© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved

[+] Provide Website Feedback



