

1445390-3 Product Details



1445390-3

TE Internal Number: 1445390-3



Miniature CPC (Circular Plastic Connector)

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- ConnectorConnector Style = Plug
- Shell Size = 8
- 4 Positions
- Accepts Wire Insulation Diameter, Range = 1.50 - 2.39 mm

Documentation & Additional Information

Product Drawings:

• ASSEMBLY, PLUG, SIZE 8 4 POSITION, SEALED, MINI CPC (PDF, English)

Catalog Pages/Data Sheets:

• AMP Circular Connectors for Commercial Signal & Powe... (PDF, English)

Product Specifications:

None Available

Application Specifications:

- Miniature Circular Plastic Connector (CPC) (PDF, English)
- Spring Probe Miniature Circular Plastic Connectors (CPC) (PDF, English)

Instruction Sheets:

None Available

CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version C1)
- 3D Model (IGES, Version C1)
- 3D Model (STEP, Version C1)

Additional Information:

Product Line Information

Related Products:

- Tooling
- Mating Products (4)
- Contacts (48)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Shell Size = 8

Housing Features:

- Connector Style = Plug
- Housing Material = Thermoplastic GF
- Housing Color = Black

Configuration Features:

Number of Positions = 4

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not reviewed for lead free solder
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:
• Accepts Wire Insulation Diameter, Range (mm [in]) = 1.50 -2.39 [0.059 - 0.094]

Other:

• Brand = TE Connectivity

