

Audio

NEUTRIK

Deutsche Version

Home

About Us

Products

Support


News

Sitemap


Search

Products only

© Neutrik® AG All rights reserved Legal Notices



3.5 mm plug, 3-pole, black metal handle, gold plated contacts







NYS 3.5 mm Plugs

NYS231BG

There are no technical infos for this product.

Product	
Electrical	
Contact resistance	< 10 mΩ
Dielectric strength	0,5 kVdc
Rated current per contact	depends on mated connector A
Mechanical	
Cable O.D.	≤ 4 mm
Material	
Contact plating	0.2 ?m Au
Contacts	CuZn39Pb3
Insert	PA 66 30 % GR
Shell	CuZn39Pb3 Black
Environmental	
Solderability	Complies with IEC 68-2-20
Temperature range	-20 °C to +70 °C
Optical	
Mobile Cables	