



Deutsche Version

Home

About Us

Products

Support

News

Sitemap

Search

Products only

© Neutrik® AG All rights reserved Legal Notices




Print

NYS228



1/4" plug, 3-pole, long turned brass handle, no rivet



					Werkstoff:	Massstabi		Datum	Name
				#)Lieferant darf ohne Ruecksprache nicht geaendert werden Zeichnung urheberrechtlich geschuetzt (DIN 34) (C)		1:1	Gezeichnet	29.01.01	Battlogg
						1.1	Geprueft		
							Gesehen		
				Benennung: 1/4" PK	none Plugs		Ersetzt durc	h:	Blatt
				NYS	228		Ersatz fuer		von Blatt
							Zeichn, Nr.		
Ind.	Aenderung	Datum	Name	REAN			3102 ST 22 21		





NYS 1/4" Plugs

NYS228

There are no technical infos for this product.

	·						
Product							
Electrical							
Contact resistance	$<$ 10 m Ω						
Dielectric strength	0,5 kVdc						
Rated current per contact	depends on mated connector A						
Mechanical							
Cable O.D.	≤ 6 mm						
Wire size	24 AWG						
Material							
Contact plating	2 μm Ni						
Contacts	CuZn39Pb3						
Insert	PA 66 30 % GR+insulation board						
Shell	CuZn39Pb3 gal 2 ?m Ni plated						
Environmental							
Solderability	Complies with IEC 68-2-20						
Temperature range	-20 °C to +70 °C						
Optical							
Mobile Cables							
	· · · · · · · · · · · · · · · · · · ·						