


**71600-604LF - Quickie® : Receptacle -
Double row - 4 Positions - 2.54 mm (0.1 in.)**



www.fci.com

Specifications

Approvals / Certifications

UL File Number	E66906
CSA File Number	LR46923
Approvals / Certifications	UL and CSA Approved

Electrical

Current rating	1 amp Continuous
Resistance (Contact)	15 m ohms max.
Resistance (Insulation)	50000 M-ohms
Voltage rating	1000V AC rms

General

Insulation Displacement Contact (IDC)	IDC Receptacle
Number of contacts (Total)	4
Number of rows	2
Polarization	Center and Dual
Strain Relief	Latching
Style	Standard Single Beam
Termination Style	IDC

Application Equipment	QP-104 QP-112 QP-106
------------------------------	----------------------------

Mating half	Mates with Low Profile Headers
--------------------	--------------------------------

Other Features

Packaging (Type)	Tube
-------------------------	------

Physical

Color (Housing)	Grey
Material (Contact)	Phosphor Bronze
Material (Housing)	Glass - Filled Thermoplastic Polyester
Plating (Contact area)	0.76 µm (30 µin.) Gold
Underplating (Contact)	1.27 µm (50 µin.) Nickel
Flammability rating	UL 94 V-0
Temperature (Range)	-65°C to +105°C