

Home Page

Linear Potentiometers

Single-Turn Potentiometers

Multi-Turn Potentimeters

Turn-Counting Dials

Industrial Joystick Controls

Industrial Foot Controllers

Valve Actuators

ROHS/WEEE

Cross Reference

ETI Systems Sales Reps

ETI Sytems Distributors

phone: 760.929.0749 eti@etisystems.com

DC27 Concentric Precision Turns Counting Dial



DC27 Concentric Turns Counting Dial

- Counts 10 turns (000 to 999 counts)
- Accuracy: ±0.35% of Voltage Ratio
- Repeatability: ±0.02% or Resolution of Pot
- High Temp. Black Plastic Housing.
- Over the Center Lock Available.
- Diameter 1-1/16"; Extension from Panel 1.24"
- Operating Temperature -30°C to +85°C

Request For Quotation (Requires User Registration)

Available Options:

Shaft Size

Over Center Lock (standard)

Comments & Special Requirements:

Quantity Required

Date Required



Return to: Turn-Counting Dials Selection Guide

Call ETI Systems at **(760)929-0749** to order by phone or for assistance with your custom application