

# Solutions for Industrial Automation



# MH22 Hybrid Precision Multi-Turn Potentiometer

#### HOME PAGE

Linear Motion Potentiometers

Single Turn Potentiometers

Multi-Turn Potentiometers

Industrial Joysticks

Foot Controllers

Valve Actuators

Turn Counting Dials

Cross Reference


ETI Systems Sales Reps

ETI Systems Distributors

# RoHS/WEEE

Contact ETI Systems at: (760) 929-0749 eti@etisystems.com





#### **MH22 Multi-Turn Potentiometer**

- Available as 3, 5, and 10 turn models
- Hybrid Element. High Temp Thermo Plastic Housing
- Bushing Mount Standard. Servo Mount Available
- Recommended for Medical Equipment (non-life support), Test and Lab Equipment, Industrial Applications
- Life Expectancy: 10 million turns
- Resistance Tolerance: ± 10% standard (± 5% special order)
- Linearity Tolerance: ± 0.3% standard (± 0.1% special order)
- Power Rating: 2 Watt (10 turn), 1 Watt (5 turn), 1 Watt (3 turn)
- Torque: 0.7 oz. in. max.
- Click here for information on Turn Counting
  Dials



For Additional Product Information,

Refer to the Multi-Turn Potentiometer Design Guide

### Request For Quotation (Requires User Registration)

## **Electrical Specifications:**

Resistance Value (1K to 100K ohms standard)

#### **Mechanical Options:**

- B Bushing Mount or -
- Servo Mount (special order)
   Number of Turns (10 turns standard)
- **HT** High Torque (special order)
- SS O-Ring Shaft Seal (special order)
- **SB** Sealed Body (special order)

Comments & Special Requirements:		
Quantity Required	Date Required	

Return to: Multi-Turn Potentiometer Selection Guide

Call ETI Systems at (760)929-0749 to order by phone

or for assistance with your custom application