

SPECIFICATIONS



RESISTANCE RANGE -----	100 TO 100K OHMS
RESISTANCE TOLERANCE -----	±5%
ACCURACY -----	±0.35% OF VOLTAGE RATIO
REPEATABILITY -----	±0.02% OR RESOLUTION OF POT
RESOLUTION -----	SEE POT SPECIFICATIONS
POWER RATING -----	2 WATTS
OPERATING TEMPERATURE -----	-30°C TO +85°C
TEMPERATURE COEFFICIENT -----	±20 PPM/°C
URNS -----	10 (000 TO 999 COUNTS)
TERMINALS -----	GOLD PLATED LUGS
LOCK -----	OVER THE CENTER
HOUSING MATERIAL -----	HIGH TEMP. BLACK PLASTIC


REV.	BY	DATE	PART NO.
			DC22

NOTES:

1. USE ETI SYSTEMS POTENTIOMETERS MODEL MW20B OR MW22B.
2. POTENTIOMETERS MAY BE 3,5,10 TURNS.
ALSO MULTIPLE GANGS.
3. DIAL AVAILABLE WITHOUT POT, ASK FOR DC27FL.
4. THREADS WILL ACCEPT PANEL THICKNESS OF 3/16 MAX.
5. SEE POTENTIOMETER CATALOG FOR ADDITIONAL SPECIFICATIONS.

*MODEL WITH MW20B IS DC20.



	SCALE	NONE	THIS DOCUMENT CONTAINS PROPRIETARY DATA OF POLARIS INDUSTRIAL ENTERPRISES, INC. NO DISCLOSURE, REPRODUCTION, OR USE OF ANY PART THERE OF MAY BE MADE EXCEPT BY WRITTEN PERMISSION.	 CARLSBAD CALIFORNIA
	DATE:	4-5-88		
	BY			
<u>TOLERANCES</u> XX = +/- .010" FRACT. = +/- 1/64" XXX= +/- .005" ANGLES = +/- 1/2° ALL SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.	APPRV'D	BT	<u>TITLE</u> POT/DIAL COMBINATION	<u>PART NO.</u> DC22
	CODE IDENT: 19477			