



[Home Page](#)

[Linear Potentiometers](#)

[Single-Turn Potentiometers](#)

[Multi-Turn Potentiometers](#)

[Turn-Counting Dials](#)

[Industrial Joystick Controls](#)

[Industrial Foot Controllers](#)

[Valve Actuators](#)

[ROHS/WEEE](#)

[Cross Reference](#)

[ETI Systems Sales Reps](#)

[ETI Systems Distributors](#)

phone: 760.929.0749

eti@etisystems.com

DA10 Concentric Precision Turns Counting Dial



DA10 Concentric Turns Counting Dial

- Counts up to 10 turns (000-999)
Positive Brake.
- Black Plastic Housing.
- Diameter - .82"; Extension from Panel - 1.42"
- Operating Temperature -30°C to +85°C
- Weight: 1.5 oz

Request For Quotation (Requires User Registration)

Available Options:

Shaft Size

Over Center Lock (standard)

Comments & Special Requirements:

Quantity Required

Date Required

Return to: [Turn-Counting Dials Selection Guide](#)

**Engineering
Drawing** (PDF)

Call ETI Systems at **(760)929-0749** to order by phone
or for assistance with your custom application