

La legrand®

Sentrex[®] and Perma Power[®]

High Performance and Computer Grade Rack Mount and CabinetMATE® Surge Protectors



he Sentrex High Performance Rack Mount Series and the Perma Power Computer Grade Rack Mount and CabinetMATE Surge Protector Series offer a wide range of solutions for communication closet, rack, and cabinet applications. By dissipating and diverting excess voltage, a Sentrex or Perma Power surge protection device keeps your critical systems functioning properly.

Surges can strike once a month or hundreds of times a day. They can penetrate a facility via AC, telephone, and communication lines, or on any wire that enters a building. Surges and noise are also generated inside a building by fluorescent lighting, electric motors, HVAC equipment and office machines. If left unprotected, sensitive communications equipment and valuable data can be damaged or destroyed.

Sentrex and Perma Power rack mount and CabinetMATE surge protectors provide advanced protection for critical electronic and communications equipment. They are an integral part of the Sentrex Zoned Approach to whole building protection.



R8BZ (Front & Back)



R5BZ20 (Front & Back)

Features & Benefits

- All lines are protected. Units provide surge and noise protection on all three modes (L-N, L-G, and N-G). Units also have thermal protection on all three lines.
- 330V UL1449 clamping level. Outstanding protection against harmful surges.
- EMI/RFI noise reduction. Protects against data disruption due to electromagnetic or radio frequency interference.
- Space saving. Rack mount units fit standard 19" [482mm] relay racks. Compact 1U design takes up minimum space. 23" [584mm] units available, consult factory.
- Low profile. CabinetMATE units offer a narrow 1 1/2" x 1 3/16" [38mm x 20mm] aluminum housing.
- Aesthetically pleasing. Rack mount units have a black matte finish and a black cord. CabinetMATE units have a gray finish and a black cord.

- Cord properly rated to load requirements. 15A units have a 14/3 SJT cord and a NEMA 5-15P plug. 20A units have a 12/3 SJT cord and a NEMA 5-20P plug.
- Lighted switch available on some units.
- Protection indication. All units have a protection indication light to show the status of the unit.
- Resettable circuit breaker. Provides overload protection.
- Product warranty. Sentrex rack mount units come with a lifetime product warranty. Perma Power rack mount and CabinetMATE Series units come with a five-year product warranty.
- UL and cUL Listed or Recognized. Rack mount units are UL and cUL Recognized to UL1449 2nd Edition standards. CabinetMATE units are UL and cUL Listed to UL1449 2nd Edition standards.

Sentrex High Performance Rack Mount Specifications				
Surge Protection Circuitry	Patented 4 element, 4 stage hybrid circuit			
UL1449 Clamping Level	330 Volts			
Actual Clamping Level	280 Volts			
Maximum Surge Current	33,000 Amps			
Noise Reduction	60 dB			
Response Time	Less than 1 nanosecond			
Product Warranty	Lifetime			

Sentrex High Performance Surge Protectors				
Catalog No./Item	Description/Specifications	Catalog No./Item	Description/Specifications	
R5S/R5S-15	High Performance Surge Protector – Six rear outlets, lighted switch. 6' [1.8m] or 15' [4.6m] cord.	R5SX/R5SX-15	High Performance Surge Protector – Six rear outlets. 6' [1.8m] or 15' [4.6m] cord.	

Perma Power Computer Grade Rack Mount Specifications				
Surge Protection Circuitry	Single Stage			
UL1449 Clamping Level	330 Volts			
Maximum Surge Current	13,000 Amps			
Noise Reduction	40 dB			
Response Time	Less than 1 nanosecond			
Product Warranty	5-Year			

	Product warranty	_	5- fear	
	Perma Power Compute	r (Grade Surge Pro	tectors
Catalog No./Item	Description/Specifications		Catalog No./Item	Description/Specifications
R8BZ/R8BZ-15	Computer Grade Surge Protector – Eight rear outlets, lighted switch. Receptacles rotated 90° and 4 outlets spaced to accommodate transformers. 6' [1.8m] or 15' [4.6m] cord.		R5BZ20/R5BZ20-15	20A Computer Grade Surge Protector – Six 20A rear outlets. On/off switch. 6' [1.8m] or 15' [4.6m] cord.
	10. 11.			c FU °us
R5BZ/R5BZ-15	Computer Grade Surge Protector – Six rear outlets, lighted switch. 6' [1.8m] or 15' [4.6m] cord.		R5BZ20X/R5BZ20X-15	20A Computer Grade Surge Protector – Six 20A rear outlets. 6' [1.8m] or 15' [4.6m] cord.
	c AL °us			c 91 0° us
R5BZX/R5BZX-15	Computer Grade Surge Protector – Six rear outlets. 6' [1.8m] or 15' [4.6m] cord.			

c**FL**°us

CabinetMATE Specifications			
Surge Protection Circuitry	Single Stage		
UL1449 Clamping Level	330 Volts		
Maximum Surge Current	13,000 Amps		
Noise Reduction	40 dB		
Response Time	Less than 1 nanosecond		
Product Warranty	5-Year		

15A CabinetMATE Surge Protectors					
Catalog No./ Item	Description/ Specifications	Catalog No./	Description/ Specifications	Catalog No./ Item	Description/ Specifications
4810BCS/ 4810BDS	CabinetMATE Surge Protector – Ten outlets. 6' [1.8m] or 15' [4.6m] cord. Length 48" [1.2m].	7011BCS/ 7011BDS	CabinetMATE Surge Protector – Eleven outlets. 6' [1.8m] or 15' [4.6m] cord. Length 70" [1.8m].	7712BCS/ 7712BDS	CabinetMATE Surge Protector – Twelve outlets. 6' [1.8m] or 15' [4.6m] cord. Length 77" [2m].
			E E E E E E E E E E E E E E E E E E E		

20A CabinetMATE Surge Protectors Catalog No.: Catalog No.: Catalog No.: Catalog No.: 7712BCS20R/7712BDS20R 2008BCS20R/2008BDS20R 4810BCS20R/4810BDS20R 7011BCS20R/7011BDS20R Description/ Description/ Description/ Description/ **Item Specifications: Item Specifications: Item Specifications: Item Specifications:** 20A CabinetMATE Surge 20A CabinetMATE Surge 20A CabinetMATE Surge 20A CabinetMATE Surge Protector - Twelve 20A Protector - Eight 20A Protector - Ten 20A outlets Protector - Eleven 20A outlets with t-slots. 6' [1.8m] with t-slots. 6' [1.8m] or outlets with t-slots. 6' outlets with t-slots. 6' [1.8m] or 15' [4.6m] cord. Length: 70" [1.8m]. or 15'. Length: 20" [508mm]. 15' [4.6m] cord. Length: [1.8m] or 15' [4.6m] cord. Length: 77" [2m]. 48" [1.2m]. c(UL)us c(UL)us c(UL)us 0

Questions? Call Technical Support today at 1-800-SENTREX.





Wiremold / Legrand

U.S. and International:

60 Woodlawn Street • West Hartford, CT 06110

1-800-621-0049 • FAX 860-232-2062 • Outside U.S. 860-233-6251

Canada:

570 Applewood Crescent • Vaughan, Ontario L4K 4B4

1-800-723-5175 • FAX 905-738-9721